

Universe	Professional
Type	Lighting
Category	Ultra-compact headlamps
Subcategory	Ultra-compact headlamps



hybrid
CONCEPT

TACTIKKA® +


Designed for the workshop, small maintenance jobs, or concerts and shows, the TACTIKKA + offers 350-lumen brightness and a mixed beam, for comfortable proximity lighting and rapid movement. It also has red lighting to ensure stealth. TACTIKKA + comes with 3 standard batteries and is also compatible with the CORE rechargeable battery, thanks to the HYBRID CONCEPT design. Mounting accessories allow the lamp to be attached to any kind of helmet.



Mixed beam for proximity and distance vision. White lighting, or red for nighttime stealth.



Headband can be undone for easy donning.



HYBRID CONCEPT design: TACTIKKA + comes with three standard batteries and is also compatible with the CORE rechargeable battery.

Short Description

Compact headlamp with mixed beam for proximity and distance vision. White lighting, or red to ensure nighttime stealth. 350 lumens

Selling Points

- Lightweight, compact and bright:
 - 350 lumens at 85 g
 - three white brightness levels for comfortable proximity lighting and rapid movement
 - red lighting (continuous or strobe) combines visual comfort and stealth
- Simple to use and practical:
 - single button for quick and easy selection of brightness or light color
 - ergonomic button, even with gloves
 - easy to put on via quick-release buckle on the headband
 - detachable, washable headband
 - HYBRID CONCEPT design: TACTIKKA + comes with three standard batteries and is also compatible with the CORE rechargeable battery
 - compatible with mounting accessories that allow the lamp to be attached to any kind of helmet
- Available in three colors, depending on use

Specification

- Brightness: 350 lumens (ANSI FL1-STANDARD)
 - Weight: 85g
 - Beam pattern: mixed
 - Energy: Three AAA/LR03 batteries (included) or CORE rechargeable battery (available as accessory)
 - Battery compatibility: alkaline, lithium or Ni-MH rechargeable
 - Certification(s): CE
 - Watertightness: IPX4 (weather-resistant)
-

Lighting performance

Lighting color	Lighting levels	Brightness	Distance	Burn time	Reserve
white	proximity	6 lm	10 m	160 h	-
	movement	100 lm	45 m	12 h	30 h
	distance vision	350 lm	90 m	2 h	60 h
red	proximity	2 lm	5 m	60 h	-
	strobe	visible at 700 m for 400 h			

Specifications by reference

Reference(s)	E089EA00	E089EA01	E089EA02
			
Color(s)	black	camo	desert
Made in	FR	FR	FR
Guarantee	5 years	5 years	5 years
Packing	1	1	1
Case quantity	50	50	50
EAN	3342540827868	3342540827875	3342540827882

Accessory(ies)

CORE
KIT ADAPT
FIXATION TACTIKKA®
SHELL L

Related product(s)

VERTEX®
VERTEX® VENT
STRATO
STRATO VENT