



ALPHA DIN transformer cabinet, H=1950mm W=1050mm D=400mm, incl. 100 mm plinth sheet-steel door, open side panels, SK1, IP30

| Model                                              |                                 |                   |     |
|----------------------------------------------------|---------------------------------|-------------------|-----|
| product brand name                                 | ALPHA                           |                   |     |
| product designation                                | Empty control cabinet enclosure |                   |     |
| design of the product                              | Surface mounting                |                   |     |
| surface processing                                 | powder-coated                   |                   |     |
| Protection class                                   |                                 |                   |     |
| protection class IP                                | IP30                            |                   |     |
| operating resource protection class                | Safety class 1                  |                   |     |
| IK protection class                                | IK09                            |                   |     |
| suitability for use for outside use                | No                              |                   |     |
| Appearance                                         |                                 |                   |     |
| RAL color number                                   | 7035                            |                   |     |
| product component                                  |                                 |                   |     |
| • cable entry                                      |                                 |                   | Yes |
| • mounting plate                                   |                                 |                   | No  |
| product extension optional side-by-side mounting   | Yes                             |                   |     |
| number of rows                                     | 36                              |                   |     |
| Mechanical Design                                  |                                 |                   |     |
| height                                             | 1 950 mm                        |                   |     |
| width                                              | 1 050 mm                        |                   |     |
| depth                                              | 400 mm                          |                   |     |
| installation depth                                 | 400 mm                          |                   |     |
| number of modular width units                      | 432                             |                   |     |
| number of modular width units per DIN mounting bar | 12                              |                   |     |
| fastening method                                   | floor mounting                  |                   |     |
| material of the enclosure                          | Steel                           |                   |     |
| Approvals Certificates                             |                                 |                   |     |
| General Product Approval                           |                                 | Test Certificates |     |
|                                                    |                                 | other             |     |



[Special Test Certificate](#)

[Miscellaneous](#)

[Confirmation](#)

| Environment                                 |                                             |  |
|---------------------------------------------|---------------------------------------------|--|
| <a href="#">Environmental Conformations</a> | <a href="#">Environmental Conformations</a> |  |

## Further information

### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1483-8KP45>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8GK1483-8KP45>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1483-8KP45](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1483-8KP45)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/8/2025 

