

Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Wheeled
- Height Adjustable
- Back Adjustable
- Seat Adjustable
- Available in different sizes

RS PRO CLEANROOM ESD Polyurethane Chair

RS Stock No.: 0687616



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested

by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO CLEANROOM ESD PU Chair is a professional solution designed for environments where effective electrostatic discharge (ESD) control is essential. It combines comfort, durability, and safety, meeting the demands of intensively used workstations.

Product Features:

- ✓ **Soft, anti-slip seat material** – ensures user comfort and effective ESD protection
- ✓ **Adjustable seat and backrest height** – allows personalized adjustment to meet individual user needs
- ✓ **Chrome-plated five-star base** – offers excellent stability and resistance to intensive use
- ✓ **Safety-First Design** – For maximum safety, the tallest model is equipped with glides instead of castors
- ✓ **Easy-to-clean surface** – resistant to dirt and does not absorb contaminants
- ✓ **Carefully designed seat and backrest shape** – provides natural spinal support and enhances comfort during prolonged sitting

An ideal solution for production and service environments where reliable protection against electrostatic discharge is required. Perfectly suited for industries such as electronics, automotive, general manufacturing, medical, pharmaceutical, and military sectors.

General Specifications

TOTAL HEIGHT (mm)	875-1200
TOTAL WIDTH (mm)	660
WEIGHT (kg)	10,5
MAX LOAD CAPACITY (kg)	120 (up to 200 kg with a special gas lift)
HEIGHT ADJUSTMENT RANGE (mm)	540-795mm
SEAT DIMENSIONS (mm)	465 x 440
BACKREST DIMENSIONS (mm)	130 x 420
ESD	YES
COLOUR	BLACK
MATERIAL	POLYURETHANE
BASE MATERIAL	ALUMINIUM
GLIDES	CONDUCTIVE
RESISTANCE GROUNDING (0hm)	$10^6 - 10^8$

Approvals

Chair compliance with standards	PN-EN IEC 61340-5-1:2025-02, PN-EN 1335-1:2004, PN-EN 1335-2:2009, PN-EN 1335-3:2009, PN-EN 1022:2007
---------------------------------	---

Similar Products

Stock No.	Brand	Product Name
06876145	RS PRO	CLEANROOM ESD PU chair, seat height adjustment 420-545mm
06876155	RS PRO	CLEANROOM ESD PU chair, seat height adjustment 505-690mm
06876175	RS PRO	CLEANROOM ESD PU Comfort chair, seat height adjustment 430-560mm
06876185	RS PRO	CLEANROOM ESD PU Comfort chair, seat height adjustment 510-700mm
06876195	RS PRO	CLEANROOM ESD PU Comfort chair, seat height adjustment 550-800mm

Accessories

Stock No.	Brand	Product Name
0687620	RS PRO	ESD castor, grey rubber tyre, diameter 50mm (**brake option available on request**)
XXX-XXX	RS PRO	ESD metal castor, diameter 50mm
0687621	RS PRO	ESD glides
0687599ESD	RS PRO	ESD footrest
XXX-XXX	RS PRO	ESD PU armrests
XXX-XXX	RS PRO	ESD armrests, black steel + antistatic PU cover
XXX-XXX	RS PRO	ESD armrests with height adjustment, black steel + antistatic PU covers