


Product Brief

# NLG Ascent Bucket™

101360



# NLG Ascent Bucket

Product code: 101360

PRODUCT BRIEF / 101360

The NLG Ascent Bucket is the world's most advanced lifting and storage bucket for working at height.

The NLG Ascent Bucket™ is the market leader in drop prevention buckets. Constructed from reinforced PVC, the lifting bucket has a safe working load of 125kg. The base is covered in a coated leather for wear and abrasion resistance and the base reinforced with a pierce and puncture resistant composite insert.

NLG Ascent Bucket™ is an ideal lifting or hoist bucket for transferring tools and materials on site and can be transformed into a tool storage system by adding the Ascent Bucket™ Liner. The 6 internal D rings are load rated anchor points for tethering tools to and remain usable after the Bucket Liner has been added.

The unique Mega Mesh™ Lock Closure on the Ascent Bucket™ allows the user to see the contents of the bucket without compromising safety as it prevents items falling out of the bucket even if inverted accidentally.

---

## INSPECTION

In addition to routine checks prior to each use, all equipment should undergo regular detailed inspection, conducted and recorded by a competent person using the NLG Inspection Checklist. If any part is worn or shows signs of degradation, immediately retire from service. In the event of a drop, quarantine the equipment for thorough inspection.

## Specification

- Heavy duty Mega Mesh™ closure system developed for easy viewing of contents even when closed
- Drop prevention closure system folds neatly out of the way when not required
- Super strong structural webbing sewn through walls and base for ultimate peace of mind
- Toughened composite base plate protects against piercing from sharp tools
- Coated leather base sleeve delivers extra wear and abrasion resistance
- Hoisting strap with burly twistlock carabiner allows secure load control when lifting with a crane or winch, as well as anchoring when stationary
- 6 integrated anchor points (5kg each) for multiple tool lanyard attachment
- External daisy chain anchor loops for PPE and staging use
- Constructed from heavy duty PVC which is both UV stabilised and mildew resistant
- Structurally engineered to withstand dynamic impact forces
- Easy wipe clean coating makes light work of maintenance
- Outer ID pocket for efficient identification
- Unique serial number for easy identification and tracking
- CE marked
- Load tested and third party certified (4:1 safety factor)
- Dimensions: 40cm (H) x 32cm (D)
- Capacity: 32 Litre
- Internal Anchor Max Load: 5KG (11lbs) Each
- Max Load: 125KG (275lbs)

---

### MAX LOAD (SWL)

125KG / 275LBS

---

### SERIAL NUMBERED

Makes the management of inspection routines and reports easy and traceable

---

### PRODUCT DATA



Weight: 1990 Grams  
 EAN (GTIN-13): 5060572180451  
 HTS Code: 6307.90.9889



Third party  
 tested and  
 certified

See the  
 Test Certificate  
 on page 5







## Breathe Safety Testing Laboratory

UKAS Testing No 8856 | Accredited to ISO/IEC17025/2005

### DROP TEST CERTIFICATE

42817DT-NLG-156360

#### PRODUCT IDENTIFICATION

**Manufacturer:**  
NLG

**Max Load (WLL):**  
125 KG (D Ring Anchor: 5 KG)

**Product:**  
Ascent Bucket

**Safety Factor:**  
5 : 1 (D Ring Anchor: 2 : 1)

**Reference:**  
101360

**Test Load:**  
625 KG (D Ring Anchor: 10 KG)

#### TEST TECHNICIAN

**Signature:**

**Name:**  
Gary Paterson

**Date:**  
23-03-17

**Position:**  
Senior Lab Technician

#### TEST RESULTS

\*D Ring Anchor Test

SAMPLE NUMBER	FACTOR 0	FACTOR 1 DROP 1	FACTOR 1 DROP 2	FACTOR 1 DROP 3	FACTOR 2 DROP 1	FACTOR 2 DROP 2	FACTOR 2 DROP 3
1	PASS	PASS*	PASS*	PASS*	PASS*	PASS*	PASS*
2	PASS	PASS*	PASS*	PASS*	PASS*	PASS*	PASS*
3	PASS	PASS*	PASS*	PASS*	PASS*	PASS*	PASS*

United Kingdom Accreditation Service

ACCREDITATION CERTIFICATE



TESTING LABORATORY  
No. 8856  
Breathe Safety Limited

Please note that the results included in this report relate only to the specific equipment samples tested. This is for the purpose of Type Approval of Equipment under the PPE Directive. For more detail refer to the full Accredited Laboratory Policy. This report may not be reproduced without authorisation from the laboratory. Any deviations from specific test methods are described in the relevant section of the report.

- Fully Equipped Laboratory for CE Type Approval Testing
- Product Trial testing for specific tests
- CE Technical File review and consultancy advice
- CE Certification facilitation through a partner Notified Body

0844 915 1111

17 Whittle Road, Ferndown Industrial Estate, Ferndown, Dorset BH21 7RL

# EU Declaration of Conformity

REFERENCE NUMBER: **364101360156**

## 01 / Manufacturer

NAME: NLG  
 ADDRESS: 6 Mannings Heath Road  
 Poole, Dorset, BH12 4NQ  
 United Kingdom

## 02 / Product

CODE: 101360  
 DESCRIPTION: Ascent Bucket  
 LOAD RATING: 125 KG / 275 LBS

## 03 / Conformity

The undersigned acting on behalf of [01] above hereby declares that:

The PPE described in [02] is in conformity with the provision and scope of our quality control and testing protocols set out in the PPE Regulation (EU) 2016/425 covering all PPE manufacturing, where such is the case, with the standard of fit for purpose design parameters. The above referred to Personal Protective Equipment [02] is identical to the equipment independently tested and certified by BSTL in accordance with EN 364:1992 test methods.

Dynamic drop performance testing conducted at 2:1 weight safety factor for tool lanyards and tether points. Static strength testing conducted at 5:1 weight safety factor for containers and storage equipment.

CERTIFICATE NUMBER: 42817DT-NLG-156360  
 ISSUED BY: BSTL, Whittle Road  
 Ferndown Ind. Estate, BH217RL, UK

## 04 / Authorised Person

I herewith certify that the equipment identified above in [02] conforms to the requirements as detailed above:

SIGNED:   
 NAME: Julian Aris  
 POSITION: Managing Director  
 DATE: 25 / 04 / 18

Tool Tethering Experts  
[neverletgo.com](http://neverletgo.com)





# NLG Ascent Bucket

Product code: 101360

View online

[neverletgo.com/ascent-bucket/](https://neverletgo.com/ascent-bucket/)

Get all the Product Briefs

[neverletgo.com](https://neverletgo.com)

**Tool Tethering Experts**  
[neverletgo.com](https://neverletgo.com)

NLG makes every effort to ensure the information in this Product Brief is accurate and current. However, NLG reserves the right to change the product specification when or if deemed necessary. NLG cannot be held responsible for any inaccuracies or omissions. Copyright © 2018. NLG ® and Never Let Go ® are registered trademarks.