

Features

- Durable and easy to install on both existing and new-build steps.
- A hard wearing, gritty surface available in bright colours helps protect against slips and trips whilst meeting the Equality Act requirements (DDA).
- Manufactured with chamfered back edge for additional safety.
- Fire Tested to: DIN 13501: Bfl - s1 (2018) & EN ISO 11925-2:2020 & EN ISO 9239-1:2010 (both 2021).
- Slip Tested to: DIN 51130 - R13 & BS 7976-2 - low slip potential.

RS PRO Black Stair Nosing 1.5m x 55mm x 55mm

RS Stock No.: 0712634



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Durable and easy to install on both existing and new-build steps.
- A hard wearing, gritty surface available in bright colours helps protect against slips and trips whilst meeting the Equality Act requirements (DDA).
- Manufactured with chamfered back edge for additional safety.
- Fire Tested to: DIN 13501: Bfl - s1 (2018) & EN ISO 11925-2:2020 & EN ISO 9239-1:2010 (both 2021).
- Slip Tested to: DIN 51130 - R13 & BS 7976-2 - low slip potential

General Specifications

Size	1.5 m x 55 mm x 55 mm
Product Height	5 mm
Colour	Black
Weight (kg)	0.9
Material	GRP
Surface Finish	Quartz grit
Min. Operating Temperature	-50°C
Max. Operating Temperature	+90°C
Environmental Resistance	Suitable for indoor and outdoor environments
Typical Applications	External steps
Installation Method	Bond or screw to surface
Cleaning Method	Product should be almost maintenance free in most outside environments. Natural elements will have the effect of cleaning product. Brushing and flushing with a mild detergent solution may be desirable now and again to restore appearance.

Approvals

Fire Tested to	DIN 13501: Bfl - s1 (2018) & EN ISO 11925-2:2020 & EN ISO 9239-1:2010 (both 2021)
Slip Tested to	DIN 51130 - R13 & BS 7976-2 - low slip potential

Similar Products

Stock No.	Brand	Product Name	Size	Colour	Weight (kg)
0712633	RS PRO	Stair Nosing	3 m x 55 mm x 55 mm	Black	1.8
0712635	RS PRO	Stair Nosing	3 m x 55 mm x 55 mm	Black/Yellow	1.8
0712636	RS PRO	Stair Nosing	1.5 m x 55 mm x 55 mm	Black/Yellow	0.9
0712637	RS PRO	Stair Nosing	3 m x 55 mm x 55 mm	Yellow	1.8
0712638	RS PRO	Stair Nosing	1.5 m x 55 mm x 55 mm	Yellow	0.9