

E524 Series Taps Specification

| Part No. | Description | Material | Finish | Thread Length | Overall Length | Pitch | Manf. Dia. |
|---------------|--------------------------|----------|--------|---------------|----------------|-------|------------|
| E524*0-80NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 7 | 41 | 80 | 1.524 |
| E524*1-72NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 8 | 41 | 72 | 1.854 |
| E524*2-64NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 9,5 | 44,5 | 64 | 2.184 |
| E524*3-56NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 9,5 | 44,5 | 56 | 2.515 |
| E524*4-48NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 12,5 | 48 | 48 | 2.845 |
| E524*5-44NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 12,5 | 48 | 44 | 3.175 |
| E524*6-40NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 14 | 50 | 40 | 3.505 |
| E524*8-36NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 9,5 | 53 | 36 | 4.166 |
| E524*10-32NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 11 | 58 | 32 | 4.826 |
| E524*12-28NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 12 | 62 | 28 | 5.486 |
| E524*1/4NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 13 | 66 | 28 | 6.35 |
| E524*5/16NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 16 | 72 | 24 | 7.938 |
| E524*3/8NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 18 | 80 | 24 | 9.525 |
| E524*7/16NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 19 | 85 | 20 | 11.112 |
| E524*1/2NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 22 | 89 | 20 | 12.7 |
| E524*9/16NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 24 | 95 | 18 | 14.288 |
| E524*5/8NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 24 | 102 | 18 | 15.875 |
| E524*3/4NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 29 | 112 | 16 | 19.05 |
| E524*7/8NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 29 | 118 | 14 | 22.225 |
| E524*1NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 35 | 130 | 12 | 25.4 |
| E524*1.1/8NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 35 | 138 | 12 | 28.575 |
| E524*1.1/4NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 41 | 151 | 12 | 31.75 |
| E524*1.3/8NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 47 | 162 | 12 | 34.925 |
| E524*1.1/2NO3 | UNF Taps, Straight Flute | HSS | BRIGHT | 47 | 170 | 12 | 38.1 |