

Universe	Professional
Type	Verticality
Category	Harnesses
Subcategory	Harnesses for fall arrest, work positioning and suspension



AVAO® SIT FAST

The AVAO SIT FAST work positioning and suspension seat harness is designed for greater comfort in all situations. Wide, semi-rigid waistbelt and leg loops give excellent support. Its lightweight, breathable construction maximizes air flow. The harness also facilitates carrying and organizing work tools, with multiple equipment loops and retainers for attaching CARITool tool holders and TOOLBAG tool-holder pouches. This seat harness is designed to be converted into a fall arrest harness when combined with a TOP chest harness, or into a rope access harness when combined with a TOP CROLL S or L chest harness. The AVAO SIT FAST features leg loops with FAST LT automatic buckles.



Wide, semi-rigid waistbelt and leg loops give excellent support. Its lightweight, breathable construction maximizes air flow.



Waistbelt and leg loops equipped with self-locking DOUBLEBACK buckles allow quick and easy adjustment.



Leg loops are equipped with FAST LT buckles for quick and easy opening and fastening without the need to readjust them, even while wearing gloves.

Short Description Comfortable seat harness for work positioning and suspension

Selling Points

- Comfortable throughout the workday: semi-rigid, wide waistbelt and leg loops for excellent support. Its lightweight, breathable construction maximizes air flow.
- Practical adjustment:
 - waistbelt equipped with self-locking DOUBLEBACK buckles for quick and easy adjustment
 - leg loops equipped with FAST LT buckles for quick and easy opening and fastening without the need to readjust them, even while wearing gloves
 - side attachment points can be folded down to prevent them snagging accidentally when not in use
- Facilitates carrying and organization of tools:
 - six pre-shaped equipment loops with protective sheath
 - two slots for CARITool tool holder
 - four slots for TOOLBAG tool pouch

Specification

- Ventral attachment point: attachment for a descender or a positioning lanyard for use in single mode
 - Lateral attachment points: attachment for a positioning lanyard for use in double mode
 - Rear attachment point on the waistbelt: restraint lanyard attachment
 - Certification(s): CE EN 358, CE EN 813, EAC
 - Material(s): nylon, polyester, aluminum, steel
-

Specifications by reference

Reference(s)	C079BA00	C079BA01	C079BA02
Color(s)	black/yellow	black/yellow	black/yellow
Size	0	1	2
Waist belt	65-80 cm	70-93 cm	83-120 cm
Leg loops	44-59 cm	47-62 cm	50-65 cm
Weight	1115 g	1130 g	1145 g
Made in	RO	RO	RO
Guarantee	3 years	3 years	3 years
Packing	1	1	1
Case quantity	6	6	5
EAN	3342540822528	3342540822535	3342540822542

Accessory(ies) CARITool
TOOLBAG

Related product(s) I'D@ S
GRILLON HOOK European version