

## Features

- **304 Stainless Steel Construction** – Offers exceptional corrosion resistance and durability, even in harsh industrial and outdoor environments.
- **Multiple Locking Points** – Features several slots on the lid and body to accommodate 13 padlocks for group lockout procedures.
- **Centralised Key Management** – Securely stores keys of locked-out equipment, allowing efficient coordination during maintenance.
- **Secure Locking Buckle** – A dedicated latch hole for team leader's padlock ensures only authorised removal of internal keys.
- **Ergonomic Handle** – Stainless-steel handle ensures comfortable and safe portability.
- Helps meet OSHA, ISO 45001, and industry-specific LOTO regulations.

## RS PRO 13 Lock Stainless Steel Group Lock Box

RS Stock No.: 0694390



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *The Stainless Steel Group Lock Boxes offer a premium solution for securely managing multiple padlock keys during group lockout/tagout (LOTO) procedures.*
- *Crafted from high-grade stainless steel, they ensure maximum durability, corrosion resistance, and long-term reliability even in harsh environments such as chemical plants, oil refineries, food and beverage production facilities, and outdoor worksites.*
- *Designed for flexibility, ease of use, and enhanced safety compliance, these lock boxes empower maintenance teams to carry out collective isolation efficiently and securely.*
- *Made of High-Grade 304 Stainless Steel for superior corrosion resistance, ideal for demanding industrial environments.*
- *Multiple Locking Slots on lid and body for group lockout participation.*
- *Ergonomic Stainless-Steel Handle for easy carrying and handling.*
- *Locking Buckle on Body for securing with a team leader's personal padlock for added security.*
- *Brushed stainless-steel finish easily stands out, even in complex work environments.*
- *Safely stores keys of locked-out equipment during group maintenance work.*
- *Allows 7 workers to lock out equipment without needing to carry individual lockouts for each isolation point.*

## General Specifications

<b>Type</b>	Group Lockout Box
<b>Material</b>	High-Grade 304 Stainless Steel
<b>Colour</b>	Silver
<b>Padlock holes</b>	13
<b>Package</b>	BOPP - Box

## Mechanical Specifications

<b>Dimensions</b>	181mm x 279mm x 103mm
<b>Height</b>	181mm
<b>Width</b>	279mm
<b>Depth</b>	103mm
<b>Weight</b>	1.5 Kgs

## Operation Environment Specifications

<b>Withstand temperature</b>	-40°C to 120°C
------------------------------	----------------