

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

APR ,2003.

ALL RIGHTS RESERVED.

APVD

LOC

DIST

REVISIONS

変更

DESCRIPTION

DATE

DWN

APVD

P

LTR

E

REVISED PER ECR-11-012674

30JUN2011

T.T

T.M

1. (参考) 塩ビケース型番: 0-368996-9

2. 取り外し用テイル付きストッパー

1. (REFER) TUBE CASE P/N: 0-368996-9

2. STOPPER WITH TAIL TO REMOVE.

表 1

(TABLE 1)

No	名称 (NAME)	材料 (MATERIAL)
①	ヘッダーハウジング (HEADER HOUSING)	PBT ガラス強化 UL94V-0 (PBT GLASS FILLED UL94V-0)
②	ポスト コンタクト (POST CONTACT)	黄銅錫めっき仕上げ (POST TIN / BRASS)

508⁻⁰

ECONOMY POWER CONN HDR ASS'Y

(11.6)

(18.2)

7.92

OBSOLETE

緑 (GREEN)	6-1123724-5	5	6-1318301-5		
黒 (BLACK)	5- -5		5- -5		
赤 (RED)	4- -5		4- -5		
青 (BLUE)	3- -5		3- -5		
黄 (YELLOW)	2- -5		2- -5		
自然色 (NATURAL)	1- -5		1- -5		
緑 (GREEN)	6- -4	4	6- -4		
黒 (BLACK)	5- -4		5- -4		
赤 (RED)	4- -4		4- -4		
青 (BLUE)	3- -4		3- -4		
黄 (YELLOW)	2- -4		2- -4		
自然色 (NATURAL)	1- -4		1- -4		
緑 (GREEN)	6- -3	3	6- -3		
黒 (BLACK)	5- -3		5- -3		
赤 (RED)	4- -3		4- -3		
青 (BLUE)	3- -3		3- -3		
黄 (YELLOW)	2- -3		2- -3		
自然色 (NATURAL)	1- -3		1- -3		
緑 (GREEN)	6- -2	2	6- -2		
黒 (BLACK)	5- -2		5- -2		
赤 (RED)	4- -2		4- -2		
青 (BLUE)	3- -2		3- -2		
黄 (YELLOW)	2- -2		2- -2		
自然色 (NATURAL)	1-1123724-2		1-1318301-2		
ピッチ (PITCH)	色 (COLOR)	数量 (QTY'S)	ヘッダーアッセンブリ型番 (HEADER ASS'Y P/N)	極数 (POS)	塩ビケース詰め型番 (TUBE PACKING P/N)

3.96

緑 (GREEN)	6-1123723-1	11	6-1318300-1		
黒 (BLACK)	5- -1		5- -1		
赤 (RED)	4- -1		4- -1		
青 (BLUE)	3- -1		3- -1		
黄 (YELLOW)	2- -1		2- -1		
自然色 (NATURAL)	1- -1		1- -1		
緑 (GREEN)	6- -0	10	6- -0		
黒 (BLACK)	5- -0		5- -0		
赤 (RED)	4- -0		4- -0		
青 (BLUE)	3- -0		3- -0		
黄 (YELLOW)	2- -0		2- -0		
自然色 (NATURAL)	1- -0		1- -0		
緑 (GREEN)	6- -9	9	6- -9		
黒 (BLACK)	5- -9		5- -9		
赤 (RED)	4- -9		4- -9		
青 (BLUE)	3- -9		3- -9		
黄 (YELLOW)	2- -9		2- -9		
自然色 (NATURAL)	1- -9		1- -9		
緑 (GREEN)	6- -8	8	6- -8		
黒 (BLACK)	5- -8		5- -8		
赤 (RED)	4- -8		4- -8		
青 (BLUE)	3- -8		3- -8		
黄 (YELLOW)	2- -8		2- -8		
自然色 (NATURAL)	1- -8		1- -8		
緑 (GREEN)	6- -7	7	6- -7		
黒 (BLACK)	5- -7		5- -7		
赤 (RED)	4- -7		4- -7		
青 (BLUE)	3- -7		3- -7		
黄 (YELLOW)	2- -7		2- -7		
自然色 (NATURAL)	1-1123723-7		1-1318300-7		
ピッチ (PITCH)	色 (COLOR)	数量 (QTY'S)	ヘッダーアッセンブリ型番 (HEADER ASS'Y P/N)	極数 (POS)	塩ビケース詰め型番 (TUBE PACKING P/N)

3.96

緑 (GREEN)	6-1123723-6	20ea	6-1318300-6		
黒 (BLACK)	5- -6		5- -6		
赤 (RED)	4- -6		4- -6		
青 (BLUE)	3- -6		3- -6		
黄 (YELLOW)	2- -6		2- -6		
自然色 (NATURAL)	1- -6		1- -6		
緑 (GREEN)	6- -5	5	6- -5		
黒 (BLACK)	5- -5		5- -5		
赤 (RED)	4- -5		4- -5		
青 (BLUE)	3- -5		3- -5		
黄 (YELLOW)	2- -5		2- -5		
自然色 (NATURAL)	1- -5		1- -5		
緑 (GREEN)	6- -4	4	6- -4		
黒 (BLACK)	5- -4		5- -4		
赤 (RED)	4- -4		4- -4		
青 (BLUE)	3- -4		3- -4		
黄 (YELLOW)	2- -4		2- -4		
自然色 (NATURAL)	1- -4		1- -4		
緑 (GREEN)	6- -3	3	6- -3		
黒 (BLACK)	5- -3		5- -3		
赤 (RED)	4- -3		4- -3		
青 (BLUE)	3- -3		3- -3		
黄 (YELLOW)	2- -3		2- -3		
自然色 (NATURAL)	1- -3		1- -3		
緑 (GREEN)	6- -2	7	6- -2		
黒 (BLACK)	5- -2		5- -2		
赤 (RED)	4- -2		4- -2		
青 (BLUE)	3- -2		3- -2		
黄 (YELLOW)	2- -2		2- -2		
自然色 (NATURAL)	1-1123723-2		1-1318300-2		
ピッチ (PITCH)	色 (COLOR)	数量 (QTY'S)	ヘッダーアッセンブリ型番 (HEADER ASS'Y P/N)	極数 (POS)	塩ビケース詰め型番 (TUBE PACKING P/N)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0-PLC ±
1-PLC ± 5±0.3
2-PLC ±
3-PLC ± >5:±0.4
4-PLC ±
ANGLES ±

MATERIAL
材料 表1参照
SEE TABLE 1

FINISH
仕上

DWN
K.KOMACHI 10APR2003

CHK
M.SHINDO 10APR2003

APVD
M.SHINDO 10APR2003

PRODUCT SPEC
製品規格
108-5609

APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

NAME
名称

TUBE PACKING 3.96 (7.92)mm PITCH
ECONOMY POWER (EP) CONN. HEADER ASSY
塩ビケース詰め3.96 (7.92) mmピッチエコパワー(EP)コネクタヘッドアッセンブリ

SIZE
A3

CAGE CODE
00779

DRAWING NO
番号
C-1318300

RESTRICTED TO

SCALE
尺度 1:1

SHEET
1 OF 1

REV
E

1470-19 (3/11)