



DT

DataTraveler Locker+ G2



USB SPEED	
READ 10MB/s*	WRITE 5MB/s*

*Based on internal testing

Automatic personal data security.

Kingston's DataTraveler® Locker+ G2 USB Flash drive automatically protects all of your portable data. Available in capacities of up to 32GB, it's easy to use, with no extra software needed, and it works interchangeably between Mac OS X and Windows systems.

For peace of mind, DataTraveler Locker+ G2 hardware encrypts and password protects data saved on the device. Simply select a password during setup and be confident that all your data has a dual layer of protection. DataTraveler Locker+ G2 comes with a built-in password manager to safely store user names and passwords for up to 20 accounts. It features a stylish, durable metal casing and a built-in key loop so it easily attaches to a briefcase, backpack or handbag. DataTraveler Locker+ G2 is backed by a five-year warranty, free technical support and legendary Kingston® reliability.

- > Hardware encryption
- > Superior password protection



Features/specs on reverse >>

DataTraveler Locker+ G2

FEATURES/BENEFITS

- > **Hardware encryption** — the best in personal security to keep your data safe
- > **Superior password protection** — user sets a password to prevent unauthorised access
- > **Versatile** — works interchangeably between Mac OS X and Windows systems
- > **Secure** — drive locks down and reformats after 10 invalid login attempts
- > **Easy to use** — no application installation required
- > **Password Manager** — access and store user names and passwords
- > **Stylish** — durable metal casing with built-in key loop
- > **Customisable¹** — Co-Logo programme available
- > **Supports** — Windows® 7, Vista® XP & Mac OS X
- > **Guaranteed** — five-year warranty with free technical support

SPECIFICATIONS

- > **Capacities²** 4GB, 8GB, 16GB, 32GB
- > **Speed³** 10MB/s read and 5MB/s write
- > **Compatibility** designed to USB 2.0 specifications
- > **No admin rights required**
- > **Minimum system requirements**
 - USB 2.0 compliant and 3.0 compatible
 - Two (2) free consecutive drive letters required for use.
- > **Dimensions** 2.28" x 0.73" x 0.38" (58.00mm x 18.6mm x 9.75mm)
- > **Operating temperature** 32°F to 140°F (0°C to 60°C)
- > **Storage temperature** -4°F to 185°F (-20°C to 85°C)



¹ Conditions apply, contact your local sales representative.

² Some of the listed capacity on a Flash storage device is used for formatting and other functions and is thus not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash Guide at kingston.com/flash_memory_guide.

³ Speed may vary due to host hardware, software and usage.

THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.

©2012 Kingston Technology Europe Ltd and Kingston Digital Europe Ltd, Kingston Court, Brooklands Close, Sunbury-on-Thames, Middlesex, TW16 7EP, England. Tel: +44 (0) 1932 738888 Fax: +44 (0) 1932 785469. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. MKD-217EN



PC MAC
ENCRYPTION
PASSWORD
SECURE
PERSONAL SECURITY
PROTECTION
AUTOMATIC
SECURE
PROTECTION
KINGSTON



COMPATIBILITY TABLE

	DataTraveler Locker+ G2
Windows® 7 (SP1)	✓
Windows Vista® (SP1,SP2)	✓
Windows XP (SP3)	✓
Mac OS X (10.5.x - 10.7.x) Intel Only	✓

KINGSTON PART NUMBERS

DTLPG2/4GB

DTLPG2/8GB

DTLPG2/16GB

DTLPG2/32GB

