

FEATURES

- Universal cable drum rewinder and unwinder
- For all types of cables and cable drums even with very small inner diameters
- Compact - lightweight -
- 1.26 kg net weight
- Loadable up to 300 kg
- Excellent for damaged cable drums
- No cable clutter
- Trouble-free and rational work approach
- Non-slip and stable base
- Can be used in combination with XB 300 and XB 500
- allows loose cable bundles and individual wires to be rolled
- Telescopic centre mandrel, extendable up to 294 mm
- this allows high cable bundles or corresponding tube bundles to be accommodated

RS PRO Cable Storage Racks & Dispensers

RS Stock No.: 2228161



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The compact X-BOARD - XB300 is a universal professional cable winder/unwinder for all small to medium cable reels.

The XB300 impresses with its small, light and flat design, but can still be loaded up to 300 kg.

Especially suitable for damaged cable drums.

It enables trouble-free and rational working without tangled cables.

6 rubberised feet ensure a non-slip and stable base. Optimal for protecting surfaces for already finished floor coverings.

Due to the removable mandrel, cable drums with different hole sizes can be used.

The multi-function mandrel has been specially developed for the X BOARD XB 300 and XB 500 cable rolling systems. Loose cable bundles can also be rolled by attaching them to the stainless steel centre mandrel of the XB 300 and then folding out the 4 side brackets. The telescopic centre mandrel measures 72 mm in diameter. It is therefore also ideal for rolling a thinner cable bundle with a small inner diameter or individual wires. The normal height of the multi-function mandrel is 196 mm, which can be extended up to max. 294 mm via the telescopic mechanism. This means high cable bundles or corresponding tube bundles can also be rolled. When the 4 side brackets are unfolded, there is a total contact surface of 430 mm in diameter. Ideally, this should correspond to the respective cable or tube bundle. A designated opening allows the unit to be combined with the RUNPOSTICKS.

Optimum area of application: rolling of loose cable bundles or individual wires up to a max. height of 294 mm and a max. diameter of 430 mm

General Specifications

Dimensions:	L 291 x B 291 x H 101 mm
Diameter:	Ø 300 mm
Weight:	1,26 kg
Drum width:	Variable
Height:	105 mm

Cable Storage Racks & Dispensers

Mechanical Specifications

Load bearing capacity:	300 kg
------------------------	--------

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
2228158	RS PRO	XB500 Cable Roller	800kg capacity		
2228160	RS PRO	XB300 Cable Roller	300kg capacity		
2228162	RS PRO	Multi-function Mandrel	For use with XB300 or XB500		



