

Logitech®

PC Headset 960 USB



Comfortable and lightweight with superior sound quality through USB connectivity

Enjoy superior digital audio quality in comfort. The Logitech® PC Headset 960 USB features a comfortable, adjustable and lightweight headband designed for comfort even when wearing it for prolonged periods. Convenient in-line controls allow easy adjustment of the volume and microphone mute; the LED indicator activates when mute is enabled. The noise-canceling microphone filters unwanted background noise, and can be adjusted to the optimal position for clearer conversations. The boom microphone rotates out of the way when not in use. Set-up is easy and fast; simply plug in the USB connector. Compatible with all major PC calling applications including Skype®, Windows Live™, Yahoo!® and AIM®. Ships in a business pack ideal for system builders, integrators and value-added resellers.

- Stylish, adjustable over-the-head design for a comfortable fit that won't slip off.
- Ultra-soft earpad, flexible and lightweight design ensures all-day comfort.
- USB cable for simple, plug-and-play connectivity.
- Adjustable boom microphone for precise positioning.
- In-line volume or mute controls for easy and precise control.
- Microphone mute indicator light tells you when mute is enabled.
- Advanced digital USB delivers superior stereo sound quality.
- Noise-canceling microphone filters background noise for clearer conversations.
- White-box business packaging is easy to ship, store and recycle.
- 3-Year warranty.



Products for
OEM & Business

Logitech®



PC Headset 960 USB

Package contents

- The Logitech® PC Headset 960 USB
- Quick start guide



Technical specifications

- Pure digital stereo audio
- Adjustable microphone boom on the left-ear side
- Extendable headband: 38mm on each side
- Noise-canceling microphone
- Frequency response
- Headphone: 20 - 20,000 Hz
- Microphone: 100 - 16,000 Hz
- Microphone sensitivity: -44dBV/PA +/-3dB
- Cable length: 8 feet
- In-line volume control position: 80cm (2.6ft) to headset
- In-line volume control with volume up/down and microphone mute/unmute button
- Mute indicator light
- Connectivity: USB

Package specifications

	Primary Pack (Single Pack)	Intermediate Pack (Inner Carton/Case Pack)	Master Shipper (Out Case Pack)
Part #	981-000100		-
Bar Code (EAN-13)	5099206008441	50992060084425	50992060084418
Weight	200g	2.400kg	10.600kg
Lenght (Width)	14.50cm	33.90cm	62.20cm
Width (Depth)	5.80cm	30.00cm	35.00cm
Height/Depth (Height)	16.10cm	15.30cm	34.20cm
Volume	1.4dm ³ (Liter)	0.01556m ³	0.07445m ³
1 Primary Pack (Single Carton)	1 Single unit	n/a	n/a
1 Intermediate Pack (Case Pack)	10 Single units	1 Intermediate Pack	n/a
1 Master Shipper (Outer Case Pack)	40 Single units	4 Intermediate Packs	1 Master Shipper
1 Pallet EURO	600 Single units	60 Intermediate Packs	15 Master Shippers
1 Container 20 ft	14400 Single units	1440 Intermediate Packs	360 Master Shippers
1 Container 40 ft	30000 Single units	3000 Intermediate Packs	750 Master Shippers