

Soldering Iron

Features

- Suitable for micro welding tasks
- Power: 50W
- Soldering accessory for soldering stations (articles 2713542 and 271354)

RS PRO Soldering Iron, 50W

RS Stock No.: 115-169



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Soldering Iron, 50W

RS brand provides alternative soldering accessories for 2713542 and 2713543 (Soldering Station). This soldering iron uses integrated soldering tips, heats rapidly. Its pluggable heating element is easy to be replaced.

Applications: majorly used for micro welding tasks.

General Specifications

Type	Soldering Iron
Power Type	Electronic
Wattage	50W
Voltage	12VDC
Temperature Range	80 °C - 480 °C
Power	50W
Size	255*45*45mm (including package)

Approvals

Declarations	REACH DoC
Certification	CE, RoHS

Similar Products

Stock No.	Brand	Product Name	Temperature Range	Power	For Use With
115166	RS PRO	Soldering Iron	80 °C - 480 °C	130 W	2713542 & 2713543 (Soldering Station)
115169	RS PRO	Soldering Iron	80 °C - 480 °C	50 W	2713542 & 2713543 (Soldering Station)
115167	RS PRO	Soldering Iron	80 °C - 480 °C	150 W	2713542 & 2713543 (Soldering Station)

Soldering Station

Stock No.	Brand	Product Name	Wattage	Tasks Support	Plug Type
271-3542	RS PRO	Soldering Station	150W	Desoldering / Soldering	UK / Euro Plug
271-3543	RS PRO	Soldering Station	130W	Desoldering / Soldering	UK / Euro Plug

Soldering Tips

Stock No.	Brand	Product Name	Shape	Size	Power Consumption	For Use With
122190	RS PRO	Soldering Tip	Conical	0.5mm	130W	Soldering Station (2713542 & 2713543) Soldering Iron (115166)
122195	RS PRO	Soldering Tip	Conical	1mm	130W	Soldering Station (2713542 & 2713543) Soldering Iron (115166)
122197	RS PRO	Soldering Tip	straight hoof	1.2mm	130W	Soldering Station (2713542 & 2713543) Soldering Iron (115166)
122203	RS PRO	Soldering Tip	Chisel	1.6mm	130W	Soldering Station (2713542 & 2713543) Soldering Iron (115166)
122199	RS PRO	Soldering Tip	straight hoof	2.4mm	130W	Soldering Station (2713542 & 2713543) Soldering Iron (115166)
122205	RS PRO	Soldering Tip	Chisel	2.4mm	130W	Soldering Station (2713542 & 2713543) Soldering Iron (115166)
122206	RS PRO	Soldering Tip	Chisel	3.2mm	150W	Soldering Station (2713542 & 2713543) Soldering Iron (115167)
122207	RS PRO	Soldering Tip	Chisel	4.6mm	150W	Soldering Station (2713542 & 2713543) Soldering Iron (115167)
122200	RS PRO	Soldering Tip	straight hoof	5mm	150W	Soldering Station (2713542 & 2713543) Soldering Iron (115167)
122193	RS PRO	Soldering Tip	Conical	1.5mm	150W	Soldering Station (2713542 & 2713543) Soldering Iron (115167)
122209	RS PRO	Soldering Tip	knife	6.9mm	150W	Soldering Station (2713542 & 2713543) Soldering Iron (115167)
122196	RS PRO	Soldering Tip	straight conical	0.3mm	50W	Soldering Station (2713542 & 2713543) Soldering Iron (115169)
122192	RS PRO	Soldering Tip	conical	0.5mm	50W	Soldering Station (2713542 & 2713543) Soldering Iron (115169)

Soldering Iron



Stock No.	Brand	Product Name	Shape	Size	Power Consumption	For Use With
122198	RS PRO	Soldering Tip	straight hoof	1.2mm	50W	Soldering Station (2713542 & 2713543) Soldering Iron (115169)
122202	RS PRO	Soldering Tip		1.3mm	50W	Soldering Station (2713542 & 2713543) Soldering Iron (115169)
122204	RS PRO	Soldering Tip	Chisel	2.2mm	50W	Soldering Station (2713542 & 2713543) Soldering Iron (115169)