

## Features

- Single interchangeable blades for use with RS PRO Insulated Screwdriver Set and Handle (2754082, 2754081 & 2754080)
- Blade bronzed, 9mm insulated hexagon shank, bevelled
- Standards IEC 60900:2004

## RS PRO Insulated Screwdriver Blades, 154mm Blades, VDE/10000V



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO VDE Interchangeable Blades

RS PRO range of VDE interchangeable screwdriver blades. The single interchangeable blades for use with RS PRO Insulated Screwdriver Set and Handle.

- *These VDE screwdriver blades are used for rapid exchange of the blades without any special tool*
- *Application for electronics jobs, automotive repair, carpentry workshops and manufacturing plants*
- *These blades are used with insulated screwdriver set and handle (2754082, 2754081 & 2754080)*

## General Specifications

Screwdriver Type	Insulated Screwdriver Blade
Tip Type	As below
Tip Size	As below
VDE/1000V Approved	Yes
Blade Length	80, 100mm
Overall Length	154mm
Blade Finish	Zinc Phosphate with Black Point

Stock No.	Product Name	Tip Type	Tip Size
0460074	Insulated Screwdriver Blade	Slotted	3.0 x 100mm
0460075	Insulated Screwdriver Blade	Slotted	3.5 x 100mm
0460076	Insulated Screwdriver Blade	Slotted	4.0 x 100mm
0460078	Insulated Screwdriver Blade	Slotted	5.5 x 100mm
0460079	Insulated Screwdriver Blade	Slotted	6.5 x 100mm
0460080	Insulated Screwdriver Blade	Phillips	1 x 80mm
0460081	Insulated Screwdriver Blade	Phillips	2 x 100mm
0460082	Insulated Screwdriver Blade	Pozidriv	1 x 80mm
0460084	Insulated Screwdriver Blade	Pozidriv	2 x 100mm
0460085	Insulated Screwdriver Blade	Torx	T10 x 100mm
0460086	Insulated Screwdriver Blade	Torx	T15 x 100mm
0460087	Insulated Screwdriver Blade	Torx	T20 x 100mm
0460088	Insulated Screwdriver Blade	Torx	T25 x 100mm
0460090	Insulated Screwdriver blade	Combo PZ/ST	PZ#1/ST x 80mm
0460091	Insulated Screwdriver blade	Combo PZ/ST	PZ#2/ST x 100mm

## Approvals

Declarations	REACH DoC
Hazardous Area Certification	N/A
Standards Met	DIN IEC 60900(VDE0682-201):2019-0460900(VDE0682-201):2019-04 IEC60900:2018

## Similar Products

Stock No.	Brand	Product Name	Type	Tip Type	Tip Size
2754080	RS PRO	Insulated Screwdriver Handle	Handle	N/A	N/A
2754081	RS PRO	Insulated Screwdriver Set, 7-Piece	VDE Screwdriver Set	Phillips/ Slotted	3,3.5,4,5.5, PH1, PH2
2754082	RS PRO	Insulated Screwdriver Set, 17-Piece	VDE Screwdriver Set	Phillips, Pozidriv, Slotted, Torx	3,3.5,4,5.5, PH1, PH2, PZ1, PZ2, SL/PZ1, SL/PZ2, T10, T15, T20, T25
0460074	RS PRO	Insulated Screwdriver Blade	Blade	Slotted	3.0 x 100mm
0460075	RS PRO	Insulated Screwdriver Blade	Blade	Slotted	3.5 x 100mm
0460076	RS PRO	Insulated Screwdriver Blade	Blade	Slotted	4.0 x 100mm
0460078	RS PRO	Insulated Screwdriver Blade	Blade	Slotted	5.5 x 100mm
0460079	RS PRO	Insulated Screwdriver Blade	Blade	Slotted	6.5 x 100mm
0460080	RS PRO	Insulated Screwdriver Blade	Blade	Phillips	1 x 80mm
0460081	RS PRO	Insulated Screwdriver Blade	Blade	Phillips	2 x 100mm
0460082	RS PRO	Insulated Screwdriver Blade	Blade	Pozidriv	1 x 80mm
0460084	RS PRO	Insulated Screwdriver Blade	Blade	Pozidriv	2 x 100mm
0460085	RS PRO	Insulated Screwdriver Blade	Blade	Torx	T10 x 100mm
0460086	RS PRO	Insulated Screwdriver Blade	Blade	Torx	T15 x 100mm
0460087	RS PRO	Insulated Screwdriver Blade	Blade	Torx	T20 x 100mm
Stock No.	Brand	Product Name	Type	Tip Type	Tip Size
0460088	RS PRO	Insulated Screwdriver Blade	Blade	Torx	T25 x 100mm
0460090	RS PRO	Insulated Screwdriver blade	Blade	Combo PZ/ST	PZ#1/ST x 80mm
0460091	RS PRO	Insulated Screwdriver blade	Blade	Combo PZ/ST	PZ#2/ST x 100mm

