

## Features

- Incorporates 3 x 10mm male studs
- Neutral and mains voltage pins are plastic
- Earth pin is metal
- 1M Ohm Resistor
- Both UK and EU options available

## RS PRO Earth Bonding Plug, 2 x Banana Socket, 1x10mm Stud

RS Stock No.: 0707107



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

### RS PRO Earth Bonding Plug, Yellow

ESD/Earth bonding plug incorporates 2 banana sockets and a 10mm male stud for connection grounding wire, designed to fit UK standard mains plug outlets.

#### Benefits and Features:

- Incorporates 2 banana sockets and a 10mm male studs for connection to ground
- #designed to fit UK standard mains plug outlets
- 1M  $\Omega$  Resistor
- Neutral and live voltage pins are plastic and therefore safe

## General Specifications

Product Type	Earth Bonding Plug
EN 61340-5-1 Compliant	Yes
Colour	Yellow
Plug Type	EU Plug

## Approvals

Conforms to	EN 61340-5-1
-------------	--------------

## Similar Products

Stock No.	Brand	Product Name	Connections	Colour
xxx-xxx 0707106	RS PRO	Earth Bonding Plug, EU Plug (no print)	3 x 10mm Male Studs	Yellow
xxx-xxx 0707107	RS PRO	Earth Bonding Plug, EU Plug	2 banana socket and a 10mm Male Studs	Yellow
xxx-xxx 0707085	RS PRO	Earth Bonding Plug, Swiss Plug	3 x 10mm Male Studs	Yellow
218-641	RS PRO	Earth Bonding Plug	3 x 10mm male studs	Yellow
218-642	RS PRO	Earth Bonding Plug	2 x Banana, 1 x 10mm male studs	Yellow
218-640	RS PRO	Earth Bonding Plug	10mm male stud	Yellow
218-647	RS PRO	Earth Bonding Plug, UK	2 x M5 Posts	Yellow
218-648	RS PRO	Earth Bonding Plug, EU	2 x M5 Posts	Yellow
218-645	RS PRO	Earth Bonding Plug, UK	1 x 10mm stud	Yellow
218-643	RS PRO	Earth Bonding Plug, EU	1 x 10mm stud	Yellow
218-644	RS PRO	Earth Bonding Plug, EU	2 x 10mm Stud – 1 x M5 Post	Yellow