



Pullers, three-armed

11210

Product no. **71035001**
GTIN **4018754342013**
Model **11210/1**

Label.

Puller Clamping w.280mm x Clamping depth390mm

Properties.

- three-armed
- with swivelling extractor hooks
- extractor hooks and beam are connected by movable tabs
- for V-belt pulleys and flywheels on long shafts
- when the spindle is tightened, the extractor hooks are tensioned and tighten
- variable clamping depth possible by adjusting the extractor hooks
- nitrided spindle, no lubrication required, maintenance-free
- zinc plated

Benefits.

Centered extraction thanks to even load distribution over 3 puller hooks.

Adjustable clamping depth for universal use.

Easy on the workpiece thanks to even force distribution.

The greater the extraction force, the stronger the grip of the extractor hooks on the workpiece to be extracted.

Particularly suitable for removing V-belt pulleys and flywheels mounted on longer shafts.


Product highlights.

For increased safety.

Thoughtfully designed, die-forged and precisely machined, hardened and tempered on state-of-the-art machines - the STAHLWILLE puller range offers numerous products for a wide range of applications. For example, terminal pullers, pullers for ball joints, counter stays or ball joint extractors - always in premium quality.



Technical drawing.



Technical attributes.

External hex drive (mm)	22 mm
Size	1
Number of hooks	3
max. load	12 t
Clamping depth (h) mm	390 mm
Spindle thread size	G 1/2 x 250
Span mm (w)	280 mm

Logistics data.

Depth mm (IFS)	455
Width mm (IFS)	210
Height mm (IFS)	175
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	620
Width (packaged, mm)	240
Height (packaging, mm)	230
Volume (packaged, dm ³)	34.224 dm ³
Product no.	71035001
Weight (gross, kg)	7,500
Weight PAP (kg)	0,812
Weight PVC (kg)	0,000
GTIN	4018754342013
Country of origin AWR	GERMANY

Region of origin	Nordrhein-Westfalen
Customs tariff no.	82055980
Packing standard	1
Weight (g)	7700 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
71035001	11210/1	Puller Clamping w.280mm x Clamping depth390mm	4018754342013
71035002	11210/2	Puller Clamping w.420mm x Clamping depth480mm	4018754342020

GTIN.



Spare part(s), spare part(s) for.



79281004
Puller spindle

Images.



STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal