



3/8" INSULATED SOCKET 1000V 6 LONG ZJHL-....

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:56:28





DESCRIPTION

3/8" INSULATED SOCKET 1000V 6 LONG

USE Manual-use sockets suitable for use with a standard ratchet or a mechanically locking ratchet. FEATURES Outer diameter reduced to a minimum for optimal accessibility on installations. Chrome vanadium steel. Socket equipped with four ogive-type recesses inside the female square to accommodate the ratchet's captive ball, ensuring a secure and reliable hold of the assembly. Presence of a collar to provide optimal electrical protection when used with a ratchet or an extension.

SPECIFIC DATA

Sales reference	Weight (g)	H (mm)	d (mm)	D (mm)	A (mm)	Guarantee
ZJHL-8	40	65	23	16	8	O
ZJHL-11	60	63	19	18	11	O

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:56:28



ZJHL-9	60	63	18	15.3	9	O
ZJHL-21	200	63	30	30	21	O
ZJHL-13	80	63	20	20	13	O
ZJHL-19	180	63	28	28	19	O
ZJHL-14	80	63	22	22	14	O
ZJHL-12	80	65	23	22	12	O
ZJHL-20	185	63	30	30	20	O
ZJHL-22	200	63	30	30	22	O
ZJHL-18	160	63	28	26	18	O
ZJHL-15	90	63	23	23	15	O
ZJHL-10	60	65	23	16	10	O
ZJHL-16	100	63	24	24	16	O
ZJHL-17	120	63	26	26	17	O

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,.-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:56:28

