

## DCH481X2-QW

54V XR FLEXVOLT SDS MAX 40mm Hammer Drill - 2 X 9Ah



5035048648995



### Product Description :

Tackle demanding jobs with this high-performance 60V MAX\* 1-9/16 in. Brushless SDS MAX Combination Rotary Hammer. Featuring a brushless motor and a German-engineered mechanism for fast drilling, this lightweight hammer delivers up to 6.1 Joules of impact energy. Built with safety in mind, this powerful tool features the anti-rotation E-CLUTCH® system and SHOCKS ACTIVE VIBRATION CONTROL®. As a Tag Ready™ product, you can seamlessly track, manage and control the 60V MAX\* 1-1/4 in. SDS PLUS Rotary Hammer in the TOOL CONNECT™ system. For user convenience, this tool is packaged with (2) 20V/60V MAX\* FLEXVOLT® batteries, a charger, and a kit box for portability on the jobsite.

### Product Features and Benefits :

- True corded performance
- Anti-rotation system detects a loss of tool control, and reacts by instantly cutting the power
- Rotation stop mode for chiselling and impact stop mode for rotary only drilling with dry diamond cores
- Brushless motor for improved runtime and reduced maintenance
- Perform & Protect: low vibration at 9.4m/s<sup>2</sup>, minimising user fatigue
- Bright white LED with delay feature improves visibility
- Ideal for drilling anchors and fixing holes into concrete, brick and masonry up to 40mm in diameter
- Compact, lightweight and ergonomic design for improved comfort and support during extended operating periods

### Technical specifications :

- Battery Capacity : 9 Ah
- Weight (Including Battery) [Metric] : 6.7 Kg
- Tool Holder [Imperial] : SDS-Max
- Vibration Measurement (Chiseling) : 8.5 m/s<sup>2</sup>
- Optimum Drilling Range [Metric] : 16 - 30 mm
- Vibration Measurement (Drilling) : 9.4 m/s<sup>2</sup>

### Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

### Included items :

- 9.0Ah XR FlexVolt Battery Packs With State of Charge Indicator (x2)
- Multi-Voltage Charger (x1)
- Multi-Position Side Handle (x1)
- Heavy Duty Carrying Case (x1)

**DCH481X2-QW**

54V XR FLEXVOLT SDS MAX 40mm Hammer Drill - 2 X 9Ah

5035048648995



Product from the series DCH481X2

Ref	◆	Titre	◆
DCH481X2-QW		54V XR FLEXVOLT SDS MAX 40mm Hammer Drill - 2 X 9Ah	