



00 21 02 SL

Tool Bag 24 parts

apprentices tool bag for electrical contractors



- semi-fold-out front with adjustable loops and exterior document compartment
- front additionally reinforced with aluminium brackets
- with galvanized steel base tray
- handle
- dimensions, interior (W x H x D): 420 x 250 x 160 mm
- contains 24 brand name quality tools, partly VDE tested according to DIN EN/IEC 60900


Article No.	00 21 02 SL
EAN	4003773032687
Dimension exterior (interior) width mm	420
Dimension exterior (interior) height mm	250
Dimension exterior (interior) depth mm	160
Net weight g	6980

technical change and errors excepted



Content 00 21 02 SL (24)

Article No.			Quantity	Nominal size	
03 05 180	Knipex	Combination Pliers	1	180 mm	
11 05 160	Knipex	Insulation Stripper	1	160 mm	
16 20 165 SB	Knipex	Dismantling Tool	1	165 mm	
25 05 160	Knipex	Snipe Nose Side Cutting Pliers, (Radio Pliers)	1	160 mm	
70 05 160	Knipex	Diagonal Cutter	1	160 mm	
98 52	Knipex	Cable Knife	1	185 mm	
361 252 1	Rennsteig	Electrician's Chisel	1	250 x 10 mm	

340 250 1	Rennsteig	Mason's Chisels	1	250 mm	
101-0300	Picard	Locksmith's hammer	1	300 g	
401-1000	Picard	Sledge hammer	1	1000 g	
75040-015	Picard	Flat brush	1	40 mm	
75075-040	Picard	Painter's spatula	1	40 mm	
71501-024	Picard	Carpenter's pencil	1	24 cm	
031580	Wera	Screwdrivers for slotted screws, 1160i	1	0,4 x 2,5 x 80 mm	
031582	Wera	Screwdrivers for slotted screws, 1160i	1	0,6 x 3,5 x 100 mm	
031587	Wera	Screwdrivers for slotted screws, 1160i	1	1,0 x 5,5 x 125 mm	
031588	Wera	Screwdrivers for slotted screws, 1160i	1	1,2 x 6,5 x 150 mm	
031601	Wera	Screwdrivers for cross recessed Phillips® screws, 1162i	1	PH1 x 80mm	
031603	Wera	Screwdrivers for cross recessed Phillips® screws, 1162i	1	PH2 x 100 mm	
031611	Wera	Screwdrivers for cross recessed Pozidriv® screws, 1165i	1	PZ1 x 80 mm	
031613	Wera	Screwdrivers for cross recessed Pozidriv® screws, 1165i	1	PZ2 x 100 mm	
005655	Wera	Voltage Detector, 247	1	0,5 x 3,0 x 70 mm	
306125	Haunstätter	PUK® Junior Hacksaw	1	150 x 240 mm	
7165/50	Nölle	Plasterer's bowl	1	125 x 90 mm	