






LOGIC™
PLUS

Data Outlets


Frontplates are available for Euro, LJU6C and MK's own modular data connectors.



Modular data frontplates are the perfect match for MK's skirting and dado trunking systems.



Prestige Plus skirting and dado.




Pinnacle bench trunking.

MK Logic Plus offers a selection of recognised standard modular frame formats which accept Euro, LJU6C and MK modular data connectors giving greater flexibility and interchangeability.

The stylish frontplates are designed for wall mounting or as a perfect match to the skirting and dado trunking ranges available from the MK Cable Management portfolio.









A comprehensive selection of data connectors including category 5 RJ45, RJ11 and BNC are available.







Data modules simply click into place from the front of the plate.

MK Data Outlet Selector













Euro Frontplates and Modules (single module size 25x50mm, double module size 50x50mm, half module size 12.5x50mm)

K182 WHI 	K184 WHI 	K5845 WHI 	K5887 WHI 	K5801 WHI 	K180 WHI 	K188 WHI 	K186 WHI 
1 GANG 2 MODULE FRONTPLATE Aperture Size: 50X50mm	2 GANG 4 MODULE FRONTPLATE Aperture Size: 100X50mm	RJ45 DATA MODULE Cat 5 TIA/EIA TSB40-A TIA/EIA 566A	RJ11/12 DATA MODULE FCC68 RJ11 - 4 wire RJ12 - 6 wire	BNC DATA MODULE 50 Ohm Crimp Style for RG5B type cable	2 MODULE BLANK	1 MODULE BLANK	HALF MODULE BLANK




LJU6C Frontplates and Modules (single module size 22x37mm)

K172 WHI 	K5745 WHI 	K5787 WHI 	K170 WHI 
1 GANG 2 MODULE FRONTPLATE Aperture Size: 22X37mm	RJ45 DATA MODULE Cat 5 TIA/EIA TSB40-A TIA/EIA 566A	RJ11/12 DATA MODULE FCC68 RJ11 - 4 wire RJ12 - 6 wire	1 MODULE BLANK




MK Modular Data Frontplates

K191 WHI 	K193 WHI 	K500 WHI 	K501 WHI 	K420 WHI 	K421 WHI 
1 GANG 1 MODULE	2 GANG 3 MODULE	25 PIN D DATA SOCKET 2 MODULE	BNC DATA SOCKET 50Ω 1 MODULE	TELEPHONE OUTLET 1 MODULE MASTER	TELEPHONE OUTLET 1 MODULE SECONDARY
K192 WHI 	K194 WHI 	K545 WHI 	K487 WHI 	K520 WHI 	K190 WHI 
1 GANG 2 MODULE	2 GANG 4 MODULE	RJ45 CATEGORY 5 DATA SOCKET 1 MODULE	RJ11 DATA SOCKET 1 MODULE	FRONTPLATE ASSEMBLY FOR IBM UNIVERSAL DATA CONNECTOR	BLANK 1 MODULE

Adaptors

VTS/4545 WHI 	VTS/4545R WHI 	VTS/35B WHI 
FLAT ADAPTOR PLATE Aperture Size: 45X45mm	RAISED ADAPTOR PLATE Aperture Size: 45X45mm	ADAPTOR BOX BASE

Monobloc Telephone and Data Accessories

K422 WHI 	K427 WHI 	K4817 WHI 
1 GANG TELEPHONE SOCKET MASTER	1 GANG TELEPHONE SOCKET SECONDARY	1 GANG RJ11 TELEPHONE/ DATA SOCKET



It's simply safer to say MK™

MK Marketing Office
King Faisal Foundation Building
PO Box 56106, Riyadh 11554
Kingdom of Saudi Arabia
Tel: +966 1 4652255 FX 6710/1/2
Direct: +966 1 4649860
Fax: +966 1 4648082

Caradon MK Electric Limited
The Arnold Centre Paycocke Road Basiidon Essex SS14 3EA
Telephone 01268 563000 Facsimile 01268 563563
e-mail: mkelectric@caradon.com
www.mkelectric.co.uk

MK Marketing Office
PO Box 60832
Deira, Dubai
United Arab Emirates
Tel: +971 4 668483
Fax: +971 4 681585