

Type	Designation	PROFITEST						METRAOHM 413	METRISO								Article
		IMBASE	MTTECH	2	C	204+	204L+		C	500D	1000D (IR)	5000D-PI	1000A	5000A	5024	GEOHM C	
<b>Modules, Adapters, Plugs, Plug Inserts, Cable Sets</b>																	
DC-II	Test instrument for AC/DC sensitive RCCBs	—	—	■	—	—	—	—	—	—	—	—	—	—	—	—	M523A
S1	Simulation model per DIN VDE 0100	■	■	■	■	—	—	—	■	■	■	—	■	—	—	—	GTM5101000R0001
PSI	PSI module (printer, memory, RS 232 interface)	—	—	—	—	■	■	—	—	—	—	■	—	—	—	—	GTM5016000R0001
SECUTEST SI/PSI	Module (printer, memory, RS 232 interface)	—	—	—	—	■	■	—	—	—	—	■	—	—	—	—	M702F/ GTM5016000R0001
A3-16	3-phase adapter 5-pole for 16A CEE outlets	■	■	■	■	—	—	—	—	—	—	—	—	—	—	—	GTZ3602000R001
A3-32	3-phase adapter 5-pole for 32A CEE outlets	■	■	■	■	—	—	—	—	—	—	—	—	—	—	—	GTZ3603000R001
A3-63	3-phase adapter 5-pole for 63A CEE outlets	■	■	■	■	—	—	—	—	—	—	—	—	—	—	—	GTZ3604000R001
3-pole adapter	3-phase meas. adapter for Schuko plug or CH, UK	—	—	■	■	—	—	—	—	—	—	—	—	—	—	—	Z521A, B, C
VARIO plug	Plug set, 3.5 ... 12 mm dia. (3 pcs.)	■	■	■	■	—	—	—	—	—	—	—	—	—	—	—	Z500A
Telearm1	Telescoping rod for PE measurement	■	■	■	■	—	—	■	■	■	■	—	■	—	—	—	GTZ3232000R0001
TR25	Reel with 25 m measurement cable	■	■	■	■	—	—	■	■	■	■	—	■	—	—	■	GTZ3303000R0001
TR50	Drum with 50 m measurement cable	■	■	■	■	—	—	■	■	■	■	—	■	—	—	■	GTY1040014E34
SP350	Earth drill, 35 cm long	■	■	■	■	—	—	—	—	—	—	—	—	—	—	■	GTZ3304000R0001
KS24	Extension cable, 4 m	■	■	■	—	—	—	—	■	■	■	—	■	—	■	—	GTZ3201000R0001
KS-C	Cable set: measurement and high-resistance measurement cable for GΩ range	—	—	—	—	—	—	—	■	—	—	—	—	—	—	—	Z541F
PRO-Schuko	Plug insert for PRO-A3 adapter (Germany)	■	■	■	—	—	—	—	—	—	—	—	—	—	—	—	GTZ3228000R0001
PRO-CH	Plug insert for PRO-A3 adapter (Switzerland)	■	■	■	—	—	—	—	—	—	—	—	—	—	—	—	GTZ3225000R0002
PRO-RSA	Plug insert for PRO-A3 adapter (South Africa)	■	■	■	—	—	—	—	—	—	—	—	—	—	—	—	Z501A
PRO-A3 II	Meas. adapter for systems, 3-phase current, phase sequence	■	■	■	—	—	—	—	—	—	—	—	—	—	—	—	Z5010
PRO-RLO II	Plug inserts for PE and other similar measurements	■	■	■	—	—	—	—	—	—	—	—	—	—	—	—	Z501P
PRO-UNI II	Plug inserts: 3 connector cables for any connection standards	■	■	■	—	—	—	—	—	—	—	—	—	—	—	—	Z501R
IrDa-USB	IR to USB interface	—	—	—	■	—	—	—	■	—	—	—	—	—	■	—	Z501J
RS 232 – USB	Adapter cable, RS 232 to USB port	—	—	—	—	—	—	—	—	—	—	■	—	—	—	—	Z501L
Z580A	Crank generator	—	—	—	—	—	—	—	—	—	—	—	—	■	—	—	Z580A
KY 5000A	Alligator clips, 2 ea.	—	—	—	—	—	—	—	—	—	—	■	—	■	—	—	Z580B
Guard 5000A	Guard cable, 1 ea. with 1 alligator clip	—	—	—	—	—	—	—	—	—	—	■	—	■	—	—	Z580C
Leadex 5000	Extension cable, 5 m	—	—	—	—	—	—	—	—	—	—	■	—	■	—	—	Z580D
<b>Current Clamps, Temperature Sensors</b>																	
WZ12C	Current clamp sensor: 1 mA ... 15 A / 1A ... 150A AC, switchable	■	■	—	—	—	—	—	—	—	—	—	—	—	—	—	Z219C
Z3512A	Current sensor clamp, 0.1 / 1 / 10 / 100 / 1000A AC, switchable	■	■	—	—	—	—	—	—	—	—	—	—	—	—	—	Z225A
E-CLIP 2	Generator clamp: 0.2 ... 1200A, 1 mA/A, 40Hz–5 kHz, 52 mm dia.	■	■	—	—	—	—	—	—	—	—	—	—	—	—	■	Z591B
T/F sensor	Sensor for temperature and relative humidity	—	—	—	—	—	—	—	■	—	—	—	—	—	—	—	Z541A
<b>Probes</b>																	
1081 probe	Triangular probe for floor measurements	■	■	■	■	—	—	—	■	■	■	—	■	—	—	—	GTZ3196000R0001
<b>Barcode Scanners / Printers</b>																	
Z502F	Barcode reader/scanner, infrared with RS 232 interface	■	■	—	—	■	■	—	—	—	—	—	—	—	—	—	Z502F
Z721D	Barcode printer	■	■	—	—	■	■	—	—	—	—	—	—	—	—	—	Z721D
Z751G	RFID reader/scanner, (13.56 MHz) with RS 232 interface	■	■	—	—	—	—	—	—	—	—	—	—	—	—	—	Z751G
<b>Chargers, Battery Sets</b>																	
Z591C	Charger with 4 NiMH rechargeable batteries	—	—	—	—	—	—	—	—	—	—	—	—	—	—	■	Z591C
NA101	Charger for 0100S battery set	—	—	■	—	—	—	—	—	—	—	—	—	—	—	—	Z501M
NA102	Charger for battery sets for C series instruments	—	—	—	■	—	—	—	■	—	—	—	—	—	—	■	Z501N
Z502H	Battery set: 8 x NiMH rechargeable	■	■	—	—	—	—	—	—	—	—	—	—	—	—	—	Z502H
<b>Pouches, Cases</b>																	
F2000	Universal pouch	■	■	■	—	■	■	—	—	—	—	■	—	■	—	—	Z700D
HC30-C	Hard case for series C testers and accessories	—	—	—	■	—	—	—	■	—	—	—	—	—	—	■	Z541C
HC40	Hard case for 2 series C testers and accessories	—	—	—	■	—	—	—	■	—	—	—	—	—	—	■	Z541D
F837	Ever-Ready Case	—	—	—	—	—	—	—	—	■	■	—	■	—	—	—	GTZ3312000R0001