SHOWA 7545 EBT

This blue, extra thin 0.10mm, 295mm long nitrile disposable glove is designed to reduce irritation and allergy risks, and provides enhanced chemical protection without compromising sensitivity. By chlorinating the glove, the feeling of tackiness is removed. The nitrile construction protects against chemical penetration and chemical splashes. The 7545 is biodegradable (Eco Best Technology®) free of latex, powder and silicone to prevent allergic reaction and skin irritation.



BENEFITS

- Disposable
- Latex-free
- Chemical-resistant
- Water-resistant
- Increased sensitivity
- Lightweight
- Forearm protection
- Biodegradable

INDUSTRIES

- Aerospace
- Automotive
- Electronics
- Food
- Healthcare
- Laboratory
- Pharmaceutical

FEATURES

- 100% Nitrile
- Silicone-free
- Chlorinated
- Powder-free
- Textured Finish

HAZARDS

- Chemical
- Single Use

GET IN TOUCH
SHOWA Interntional | WTC - Tower 2 - Strawinskylaan 1077 XX Amsterdam - The Netherlands
showagroup.com | info@showagroup.eu
© SHOWA GROUP 2024 | All rights reserved

SHOWA 7545 EBT

NORMS & CERTIFICATES

Cat III



2777

EN ISO 374-1:2016+A1:2018/Type B



JKOPT

EN ISO 374-5:2016



VIRUS

Food Contact





TRADES & APPLICATIONS

- Intricate parts handling
- Light assembly of oil-coated pieces
- Painting & spray workshops
- HoReCa
- Emergency services
- Medical
- Cytostatics
- Laboratory, pharma & analysis
- Pharmaceuticals and API

PACKAGING

- Dispenser par case: 10
- Gloves per dispenser: 100
- Gloves per case: 1000
- Packaging info - XXL size: 90

THICKNESS

0.10 mm

LENGTH

295 mm

COATING

- Nitrile
- Biodegradable

LINERS

- Unsupported

SIZES

6-7/S | 7-8/M | 8-9/L | 9-10/XL | 10-11/XXL

COLOUR

- Blue

MATERIAL

- Single use

USER INSTRUCTIONS

Gloves provide protection from chemical and mechanical hazards shown. Do not use gloves that show signs of wear. If required, cleanse outer surface of glove with running water. Discard used gloves in compliance with local regulations. Do not wear gloves when there is a risk of entanglement by moving parts of machines.

DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

GET IN TOUCH
SHOWA Interntional | WTC - Tower 2 - Strawinskylaan 1077 XX Amsterdam - The Netherlands
showagroup.com | info@showagroup.eu
© SHOWA GROUP 2024 | All rights reserved