



MASTER TL5 High Output

MASTER TL5 HO 49W/865 SLV/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	30000 h
Features	na [Not Applicable]
System Description	High Output
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux (Nom)	4550 lm
Luminous Flux (Rated) (Nom)	4075 lm
Color Designation	Cool Daylight
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	92 lm/W
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	83 lm/W

Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %
Operating and Electrical	
Power (Nom)	49.2 W
Lamp Current (Nom)	0.255 A
Temperature	
Design Temperature (Nom)	35 ℃

Datasheet, 2020, March 19 data subject to change


MASTER TL5 High Output

Controls and Dimming		
Dimmable	Yes	
Mechanical and Housing		
Cap-Base Information	Green Plate	
Approval and Application		
Energy Efficiency Label (EEL)	A+	
Mercury (Hg) Content (Nom)	1.4 mg	
Energy Consumption kWh/1000 h	54 kWh	
Product Data		
Full product code	871150064389655	

Order product name	MASTER TL5 HO 49W/865 SLV/40
EAN/UPC - Product	8711500643896
Order code	927927586555
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927927586555
Net Weight (Piece)	127.400 g
ILCOS Code	FDH-49/65/1B-L/P-G5-16/1450

Warnings and Safety

Dimensional drawing




Product


MASTER TL5 HO 49W/865 SLV/40

TL5 HO 49W/865

Photometric data








LDPO_TL5-HO8_865-Spectral power distribution Colour

MASTER TL5 High Output


Lifetime





LDLE_TL5-HO8_0001-Life expectancy diagram





LDLM_TL5-HO8_0001-Lumen maintenance diagram



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.