

## CV 30/1 UPRIGHT CARPET DRY VACUUM CLEANER

Kärcher CV 30/1: Powerful upright carpet cleaner. 300mm width, adjustable brush, clean deep into the carpet pile. Detachable suction tube for vacuuming upholstery and hard-to-reach areas.



Order no.

1.023-117.0

### Technical data

EAN code		4054278495064
Current type	V / Hz	220 - 240 / 50 - 60
Working width	cm	30
Vacuum	mbar / kPa	193 / 19.3
Air flow	l/s	43
Container content	l	5.5
Standard nominal width		ID 35
Cable length	m	12
Sound pressure level	dB(A)	66
Colour		anthracite
Weight without accessories	kg	8.4
Weight incl. packaging	kg	11.4
Dimensions (L × W × H)	mm	340 × 310 × 1215

### Equipment

Crevice nozzle		■
Upholstery nozzle		■
Detachable suction tube		■
Corrugated suction hose		■
Quantity of filter bags	Piece(s)	1
Filter bag material		Paper
Filter status indicator		■
Plug-in power cord		Standard
Height-adjustable handle		■
Protection class		II
Brush roller standard	Piece(s)	1
filter foam	Piece(s)	1

■ Included in delivery.



### Manual brush roller adjustment

- Thanks to the height adjustment, the roller brush can be adjusted to any carpet pile height.

### Brush replacement without tools

- Rapid change of roller brush without the need for any tools.

### Quick-change system for power cable

- Time- and cost-saving replacement of power cable without any prior knowledge.

## EQUIPMENT FOR CV 30/1 UPRIGHT CARPET DRY VACUUM CLEANER 1.023-117.0



	Order no.	Description	
<b>SUCTION NOZZLES</b>			
<b>Crevice nozzles</b>			
Crevice nozzle DN35	1 6.906-240.0	Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 250 mm.	<input checked="" type="checkbox"/>
<b>Upholstery nozzles</b>			
Upholstery nozzle complete NW35	2 6.905-998.3		<input type="checkbox"/>
<b>UPRIGHT BRUSH-TYPE VACUUM CLEANER ACCESSORY</b>			
Roller brush	3 6.906-642.0	Hard red bristles (e.g. for needle felt).	<input checked="" type="checkbox"/>
	4 6.906-641.0		<input type="checkbox"/>
<b>FURTHER ACCESSORIES DRY VACUUM CLEANERS</b>			
Set hand nozzle	5 2.889-361.0		<input type="checkbox"/>
<b>FILTER BAGS</b>			
<b>Fleece filter bags (3 ply)</b>			
Fleece filter bags, 10 Piece(s), CV 30/1, CV 38/1, CV 38/2, CV 48/2	6 6.904-305.0	3-ply tear-resistant fleece filter bags, dust class M, standard for CV 30/1 and CV 38/1. Contents: x10.	<input type="checkbox"/>
<b>Paper filter bags</b>			
Paper filter bags, 10 Piece(s), CV 30/1, CV 38/1, CV 38/2, CV 48/2	7 6.904-294.0	Paper filter bags, dust class M suitable for all CV 30/1 and CV 38/1 models. Contents: x10.	<input type="checkbox"/>
<b>FILTER T/ NT</b>			
<b>HEPA filter for dust class H</b>			
Filter complete packaged HEPA	8 2.889-286.0		<input type="checkbox"/>

■ Included in delivery. □ Available accessories.