

BMP[®]21-PLUS

LABEL PRINTER



Tough on the Outside. Smart on the Inside.

Once you experience the BMP[™]21-PLUS Label Printer's unstoppable labelling power, you're not going to want to share. It combines a tough exterior with smart printing capabilities for wires, cables and flat surfaces

- Drop-lock-and-print cartridges
- Super rugged with moulded rubber bumpers
- Rechargeable lithium-ion battery
- 7 durable continuous materials with widths from 6 to 38.10 mm
- Automatic label formatting for wire wraps, terminal blocks, patch panels and cable flags and general banner labels
- 104 symbols for electric, smart home, safety and datacom
- Label grabber, printer holds label after cutting
- Standard 2 year warranty

Order Reference	Description	Width (mm)	Length (m)	Manufacturer Part Number	Printer Compatibility
B-595 Indoor/Outdoor Vinyl for General Industrial Marking					
7374667	Black on orange vinyl tape, 12.7mmx6.4m	12.70 mm	6.40 m	M21-500-595-OR	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
7374658	Black on orange vinyl tape, 9.53mmx6.4m	9.53 mm	6.40 m	M21-375-595-OR	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949140	Black on white vinyl tape, 12.7mmx6.4m	12.70 mm	6.40 m	M21-500-595-WT	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949144	Black on white vinyl tape, 19.05mmx6.4m	19.05 mm	6.40 m	M21-750-595-WT	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949147	Black on white vinyl tape, 9.53mmx6.4m	9.53 mm	6.40 m	M21-375-595-WT	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949184	Black on yellow vinyl tape, 12.7x6.4m	12.70 mm	6.40 m	M21-500-595-YL	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949153	Black on yellow vinyl tape, 19.05x6.4mm	19.05 mm	6.40 m	M21-750-595-YL	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949181	Black on yellow vinyl tape, 9.53mmx6.4m	9.53 mm	6.40 m	M21-375-595-YL	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
7374642	White on blue vinyl tape, 12.7mmx6.4m	12.70 mm	6.40 m	M21-500-595-BL	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949156	White on blue vinyl tape, 19.05mmx6.4m	19.05 mm	6.40 m	M21-750-595-BL	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
7374648	White on blue vinyl tape, 9.53mmx6.4m	9.53 mm	6.40 m	M21-375-595-BL	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
7374654	White on green vinyl tape, 12.7mmx6.4m	12.70 mm	6.40 m	M21-500-595-GN	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949150	White on green vinyl tape, 19.05x6.4m	19.05 mm	6.40 m	M21-750-595-GN	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
7374651	White on green vinyl tape, 9.53mmx6.4m	9.53 mm	6.40 m	M21-375-595-GN	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949162	White on red vinyl tape, 19.05mmx6.4m	19.05 mm	6.40 m	M21-750-595-RD	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
B-430 & B-488 Polyester Strips for Component Marking					
6949119	Black on Clear Polyester 12.7mm X 6.4m	12.70 mm	6.40 m	M21-500-430	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949112	Black on White Polyester 12.7mm X 6.4m	12.70 mm	6.40 m	M21-500-488	BMP21-PLUS; BMP21; IDPAL
6949116	Black on White Polyester 19.05mm X 6.4m	19.05 mm	6.40 m	M21-750-488	BMP21-PLUS; BMP21; IDPAL
B-499 Nylon Cloth Wire & Cable Wraps					
6949106	Black on White Nylon Cloth 12.7mm X 4.87m	12.70 mm	4.88 m	M21-500-499	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949100	Black on White Nylon Cloth 19.05mm X 4.87m	19.05 mm	4.88 m	M21-750-499	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949103	Black on White Nylon Cloth 9.53mm X 4.87m	9.53 mm	4.88 m	M21-375-499	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
B-342 Permasleeve[™] Heat-Shrink Wire & Cable Markers					
6949125	Black on White Heatshrink Sleeve 3.18mm X 2.13m	6.00 mm	2.10 m	M21-125-C-342	BMP21-PLUS
6949128	Black on White Heatshrink Sleeve 4.75mm X 2.13m	8.50 mm	2.10 m	M21-187-C-342	BMP21-PLUS; BMP21; IDPAL
6949122	Black on White Heatshrink Sleeve 6.35mm X 2.13m	11.15 mm	2.10 m	M21-250-C-342	BMP21-PLUS; BMP21; IDPAL
6949131	Black on White Heatshrink Sleeve 9.53mm X 2.13m	16.40 mm	2.10 m	M21-375-C-342	BMP21-PLUS; BMP21; IDPAL
B-427 Self Laminating Wire & Cable Wraps					
6949138	Black on White/Transparent Self-Laminate label, print area 12.7mm	38.10 mm	4.30 m	M21-1500-427	BMP21-PLUS; BMP21
7374664	Black on White/Transparent Self-Laminate label, print area 12.7mm	30.48 mm	4.30 m	M21-1250-427	BMP21-PLUS; BMP21
6949134	Black on White/Transparent Self-Laminate label, print area 9.53mm	25.40 mm	4.30 m	M21-1000-427	BMP21-PLUS; BMP21
7374660	Black on White/Transparent Self-Laminate label, print area 9.53mm	19.05 mm	4.30 m	M21-750-427	BMP21-PLUS; BMP21
B-499 Nylon Strips for Terminal Block Marking					
6949175	Black on White Terminal Block Tape 12.7mmx4.87m	12.70 mm	4.90 m	M21-500-499-TB	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
6949166	Black on White Terminal Block Tape 9.53mmx4.87m	9.53 mm	4.90 m	M21-375-499-TB	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
Accessories					
8294694	BMP21-PLUS-BATT			BMP21-PLUS-BATT	BMP21-PLUS; BMP21-LAB
8294691	BMP21-PLUS-HC			BMP21-PLUS-HC	BMP21-PLUS; BMP21-LAB; BMP21
6949188	Thermal Transfer Printer AC Adaptor EU			BMP21-AC EUR	BMP21
6949093	Thermal Transfer Printer AC Adaptor UK			BMP21-AC UK	BMP21