



Handling protection

# TITAN 397



EN388



4111X

CATEGORY 2



DEXTERITY

EN420:  
5/5

## Comfort and dexterity for common handling tasks

### SPECIFIC ADVANTAGES



#### Comfort

- Excellent comfort, due to the thickness of the cotton lining and the ventilated back
- Freedom of movement: dexterity and flexibility, due to the close fit to the hand



#### Durability

- Longer service life: good abrasion resistance



#### Skin protection

- Free of harmful substances: DMF Free



#### Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

### INDUSTRIES

- Automotive/mechanical industry
- Other industries

### APPLICATIONS

- Construction materials handling
- Manufacturing small electrical components
- Handling oily mechanical parts
- Part assembly
- Precision mechanical work
- Sanding



Handling protection

# TITAN 397

## LEGENDS

|                                                                                  |     |                                       |           |
|----------------------------------------------------------------------------------|-----|---------------------------------------|-----------|
| EN388                                                                            |     | MECHANICAL HAZARDS                    |           |
|  |     | PERFORMANCE LEVELS (X = NOT TESTED)   |           |
| 4                                                                                | 1   | 1                                     | X         |
| 0-4                                                                              | 0-5 | 0-4                                   | 0-4 A-F P |
|                                                                                  |     | Impact protection (optional)          |           |
|                                                                                  |     | Cut resistance according to ISO 13997 |           |
|                                                                                  |     | Puncture resistance                   |           |
|                                                                                  |     | Tear resistance                       |           |
|                                                                                  |     | Blade cut resistance                  |           |
|                                                                                  |     | Abrasion resistance                   |           |

## PRODUCT DETAILS

|                                                                                         |                 |
|-----------------------------------------------------------------------------------------|-----------------|
| Interior finish                                                                         | Textile support |
| Exterior finish                                                                         | Smooth          |
| Material                                                                                | Nitrile         |
| Cuff characteristic                                                                     | Knitted Cuff    |
| Colour.s                                                                                | Yellow Beige    |
| European sizes                                                                          | 6 7 8 9 10      |
| Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)  | 1.1E+10 Ω       |
| Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity) | 9.1E+8 Ω        |

## LOGISTIC DETAILS

|           |                                                |
|-----------|------------------------------------------------|
| Packaging | 1 pair/bag<br>10 pairs/bag<br>100 pairs/carton |
|-----------|------------------------------------------------|

## LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/07/18/1377
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE