

# CONTROL DEVICES AND OTHER ACCESSORIES

## Time Switches and Modular Contactors



412790

Part No	Description
03705	Digital time switch weekly 1 channel with 6 year battery reserve
412780	Analogue time switch daily 1 channel
412790	Analogue time switch daily 1 channel with 100h battery reserve
412523	Modular contactor 230V a.c 2NO 25A 1 module
412535	Modular contactor 230V a.c 4NO 25A 2 module
412536	Modular contactor 230V a.c 4NC 25A 2 module

## Energy Metering



004670

Part No	Description
004670	Energy Meter single Phase 32A Direct connect 1 Module
004678	Energy Meter single Phase 63A Direct connect 2 Module

## Surge Protection Devices



412220

Part No	Description
412220	Surge Protection Device 1P 20KA/Pole 1 module
412230	Surge Protection Device 1P 40KA/Pole 1 module
412233	Surge Protection Device 4P 40KA/Pole 4 module

FOR PROXIMITY SURGE PROTECTION USE LEGRAND EXCEL LIFE SURGE PROTECTION MODULE SERIES



EM803SURGEWE



ED777XWE



TO DOWNLOAD  
THE CATALOGUE  
SCAN THE QR CODE

# MODULAR PROTECTION DEVICES



TRUSTED PROTECTION  
FOR YOUR RESIDENTIAL  
INSTALLATION



**Legrand Australia**  
Building 4, Nexus Industry Park  
43-47 Lyn Parade, Prestons NSW 2170  
Tel.: 1300 369 777  
www.legrand.com.au

**HPM Legrand New Zealand**  
106-124 Target Road  
Glenfield, Auckland 0627  
Tel.: 0800 476 009  
www.legrand.co.nz

07/2017

HPML0761

CATALOGUE  
PAGES  
INSIDE

THE GLOBAL SPECIALIST IN ELECTRICAL  
AND DIGITAL BUILDING INFRASTRUCTURES



# MODULAR PROTECTION DEVICES FOR RESIDENTIAL INSTALLATIONS

## ISOLATING (MAIN) SWITCHES

The DX<sup>3</sup> isolating (main) switch range with AC22A utilisation category is suitable for resistive and inductive loads with frequent operation for higher safety and easier maintenance:

- 63A and 100A
- 1 pole and 3 pole

## COMPACT 1 MODULE RCBO


The new DX<sup>3</sup> compact RCBO allows for reliable and consistent electrical operation in residential buildings. This device has a neutral switching for added safety and is Type A to reduce unwanted tripping:

- 6A to 32A
- 1 module – 30mA
- Type A

## MCB

The new TX<sup>3</sup> MCB range ensures safe installation and operation for maximum protection of people and property. For ease of installation, wiring and maintenance, this range has a number of features to save time at each stage of a project:

- 6A to 63A
- 1 pole to 3 pole
- 6kA breaking capacity



## SURGE PROTECTION DEVICES

The new Legrand surge protection devices ensure optimum protection for electronic equipment, while providing a universal solution suited to the installation practices of all residential applications, covering all levels of discharge currents suitable for residential buildings.

## MODULAR CONTACTOR

The CX<sup>3</sup> range of modular contactors allows for consistent control. Low noise contactors for sensitive applications and manual override handle to test and control the circuit manually, making the range suitable for all applications:

- 16A to 63A
- Multiple contact configurations (NC/NO)
- Status indicator

## TIME SWITCHES

The trusted analogue and digital time switches saves energy and reduce costs. This range covers all simple and complex applications with replaceable reserve battery for easy and fast maintenance, and removable timer module for easy bench programming:

- Analogue with horizontal and vertical dial (daily and weekly)
- Digital (daily, weekly and yearly)
- Programmable on computer



## ERGONOMIC LABEL HOLDER

For easy maintenance and simple circuit identification




## BOTTOM TERMINALS

Compatible with fork or prong type busbars



## WIRE GUIDE FLAP

Avoids connection errors for an increased safety level



## TWO POSITION DIN CLIP

Allows independent breaker removal with supply busbar in place for easy maintenance

# CIRCUIT PROTECTION RANGE

## Isolating (Main) Switches

Part No	Description
406412	1P Isolating Switch 63 A 1 Module
406423	1P Isolating Switch 100 A 1 Module
406461	3P Isolating Switch 63 A 3 Module
406469	3P Isolating Switch 100 A 3 Module



406412

## MCB

Part No	Description
403430	6A - 6kA - C curve
403432	10A - 6kA - C curve
403434	16A - 6kA - C curve
403435	20A - 6kA - C curve
403436	25A - 6kA - C curve
403437	32A - 6kA - C curve
403438	40A - 6kA - C curve
403439	50A - 6kA - C curve
403440	63A - 6kA - C curve



403430



403551

## RCBO

New Part No*	Old Part No	Description
411128	602780	Compact RCBO 6A 6kA 30mA 1 Module A type
411129	602782	Compact RCBO 10A 6kA 30mA 1 Module A type
411131	602783	Compact RCBO 16A 6kA 30mA 1 Module A type
411132	602784	Compact RCBO 20A 6kA 30mA 1 Module A type
411133	602785	Compact RCBO 25A 6kA 30mA 1 Module A type
411134	602786	Compact RCBO 32A 6kA 30mA 1 Module A type



411128

\*New part numbers are neutral switching and reversible power supply.

## RCCB

Part No	Description
411510	2P RCCB 40A 30mA 2 Module
411511	2P RCCB 63A 30mA 2 Module
411708	4P RCCB 40A 30mA 4 Module
411709	4P RCCB 63A 30mA 4 Module



411510

## Busbar

Part No	Description
404911	Prong type bus bar 12 module
404926	Fork type bus bar 13 module
404905	Terminal Adaptor - 4 to 25mm <sup>2</sup>



404911

## Load Centre

Part No		Description
Flush mount	Surface mount	
HL12F	HL12S	Load centre 12 way
HEE18F	HEE18S	Load centre 18 way
HL24F	HL24S	Load centre 24 way
HL36F	HL36S	Load centre 36 way



HL12S