

CAL16-11A



Products Low Voltage Products and Systems Control Products Contactors Block Contactors Accessories

Parts & Services Low Voltage Products and Systems Control Products Arc Guard Systems Service Spares and Consumables

General Information

Extended Product Type:	CAL16-11A
Product ID:	SK829002-A
EAN:	7320500002964
Catalog Description:	AUX. CONTACT#CAL16-11A
Long Description:	2 pole screw type left side mounted auxilliary contact block, instantaneous N.O. and N.C. contacts, suitable for standard industrial environments

Ordering

EAN:	7320500002964
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369001

Dimensions

Product Net Width:	12.5 mm
Product Net Height:	68 mm
Product Net Depth:	70 mm
Product Net Weight:	0.05 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	100 mm
Package Level 1 Height:	18 mm
Package Level 1 Length:	100 mm
Package Level 1 Gross Weight:	0.064 kg

Environmental

Battery Information:	Type NONE
-----------------------------	-----------

Additional Information

Connecting terminals (delivered in open position):	M 3.5 (+,-) pozdriv 2 screw with cable clamp
Conventional Free-air Thermal Current (I_{th}):	acc. to IEC 60947-5-1, $q=40^{\circ}\text{C}$ 16 A
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20
Minimum switching capacity [V/mA]:	0.25 VA/ 12 V / 5 mA
Power Loss:	Per Pole 0.2 W
Product Main Type:	CAL16
Product Name:	AUX. CONTACT
Rated Breaking Capacity acc. to IEC 60947-5-1:	10 x I_e AC-15
Rated Frequency (f):	Supply Circuit 50 Hz Supply Circuit 60 Hz
Rated Insulation Voltage (U_i):	acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Rated Making Capacity acc. to IEC 60947-5-1:	10 x I_e AC-15
Rated Operational Current AC-15 (I_o):	(220 / 240V) 6 A (24 / 127V) 6 A (380 / 440V) 4 A (500V) 1 A (690V) 1 A

Rated Operational Current DC-13 (I_b): (125V) 1.8 A
(24V) 6 A
(250V) 0.6 A
(48V) 6 A
(72V) 4 A

Rated Short-time Withstand Current (I_{cw}): for 0.1s 100 A
for 1.0s 50 A

Replaced Product ID (OLD): 9262465-525

SK829001-A

Suitable For: A-line

Suitable for Product Class: CONTACTORS

Technical Information: AUXILIARY CONTACT

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SFA1-46

Classifications

ETIM 4.0: EC000041 - Auxiliary contact block

ETIM 5.0: EC000041 - Auxiliary contact block

Object Classification Code: K

UNSPSC: 39121500

