

Protective hose - WP-SPIRAL PU C HF 17 - 3240858

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Protective hose, spring steel wire with PU coating, highly stranded, 1 Pcs. / Pkt. = roll à 10 m

The figure shows a version of the article



Key commercial data

Packing unit	10 M
Minimum order quantity	10 M
GTIN	 4 046356 736848
Weight per Piece (excluding packing)	99.99 g
Custom tariff number	39173200
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Inner diameter (f)	13.00 mm
Outside diameter	17.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Short-term temperature	120 °C

General

Color	blue
Type	Spring steel wire with PU coating
Components	free from silicone, halogen, and cadmium
Inflammability class according to UL 94	V2
Material	PU
Bending radius, static	13.00 mm

Protective hose - WP-SPIRAL PU C HF 17 - 3240858

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals


Approvals

VDE Zeichengenehmigung

Ex Approvals

Approvals submitted

Approval details

VDE Zeichengenehmigung 
--

Accessories

Accessories

Corrugated pipe screw connection

Protective hose - WP-SPIRAL PU C HF 17 - 3240858

Accessories

Screw connection - WP-G PP HF PG11 - 3240990



Cable gland made from PP with Pg thread, IP65 protection

Screw connection - WP-G PP HF M16 - 3240997



Cable gland made from PP with metric thread, IP65 protection

Screw connection - WP-GT PP HF PG11 - 3241004



Cable gland made from PP with Pg thread, rotatable, IP54 protection

Screw connection - WP-GT PP HF M20 - 3241012



Cable gland made from PP with metric thread, rotatable, IP54 protection

Mounting material

Hose clamp - WP-BASE HF 17 - 3240969



Hose clamps

Protective hose - WP-SPIRAL PU C HF 17 - 3240858

Accessories

Protective hose fixing bracket - WP-BASE A M16 - 3241083



Fixing bracket for protective sleeves, fixed with two screws

Protective cap

Cable protection end sleeve - WP-SC HF 17 - 3241018



End sleeves as cable protection