

# Precision Knives and Blades

- A fine selection of six knives from lightweight to heavy-duty for the professional and hobbyist
- Precision made for durable life
- Interchangeable blades held firm in sure-locking four jaw chuck
- Stay sharp blades are made from surgical steel and honed for closest cutting and long lasting edge

## Light-duty Precision Knives



- Designed for light-duty cutting on paper, soft and light-weight materials or wood

Cat No.	UPC No.	Packed	Length		Type of blade	Shelf Pack
			Inch	mm		
<b>XN100</b>	037103487681	Boxed	5 13/16	148	XNB103	6
<b>XN100B</b>	037103488466	Boxed	Same as XN-100 – Tube			24

## Medium-duty Precision Knife



- Designed for heavy paper and medium density materials

Cat No.	UPC No.	Packed	Length		Type of blade	Shelf Pack
			Inch	mm		
<b>XN200</b>	037103487698	Boxed	5 3/4	146	XNB205	6

## Heavy-duty Plastic Handle Precision Knife



- Designed for working with hardwood, plastic and other difficult to cut materials

Cat No.	UPC No.	Packed	Length		Type of blade	Shelf Pack
			Inch	mm		
<b>XN210</b>	037103487704	Boxed	5 7/16	137	XNB201	6

## Carving Precision Knife



- For those who prefer a metal handled knife
- Cuts through hardwood and plastics

Cat No.	UPC No.	Packed	Length		Type of blade	Shelf Pack
			Inch	mm		
<b>XN300</b>	037103487728	Boxed	5 5/8	144	XNB301	6

# Light and Medium-duty Knife Set

- For a wide range of cutting operations
- Contains 10 assorted blades



Cat No.	UPC No.	Packed	Description	Shelf Pack
<b>XNS100</b>	037103487742	Boxed	XN100 and XN200 knives & 10 assorted blades	6

## Replacement Blades

- Blades interchangeable with other similar knives
- Safely packed in transparent plastic containers and carded
- Bulk packed
- Number of blades per container shown in tables



**XNB301** Straight Carving



**XNB305** Curved Carving



**XNB103** Fine Pointed



**XNB203** General-Purpose



**XNB105** Stencil



**XNB205** Pointed



**XNB201** Chisel



**XNB101** Standard

Cat No.	UPC No.	Qty.	Description	Fits Knife	Shelf Pack
<b>XNB103</b>	037103487766	5	For most detailed cutting and stripping	XN100	6
<b>XNB103B</b>	037103488473	100	For most detailed cutting and stripping	XN100	1
<b>XNB203</b>	037103487797	5	For most cutting requirements	XN200/210/300	6
<b>XNB105</b>	037103487773	5	For scoring and etching as well as stencil cutting	XN100	6
<b>XNB205</b>	037103487803	5	For close corner cuts on templates, mates, gaskets, also trimming, stripping and de-burring	XN200/210/300	6
<b>XNB201</b>	037103487780	5	Rough shaping de-burring and chiseling	XN200/210/300	6
<b>XNB101</b>	037103487759	5	General-duty for cutting, carving and correcting stencils	XN100	6
<b>XNB301</b>	037103487834	2	For general-purpose carving	XN300	6
<b>XNB305</b>	037103487858	2	For smoothing and shaping	XN300	6