

WCC 38 - Cable clamp

3240258

<https://www.phoenixcontact.com/gb/products/3240258>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable clamp, for DIN rails



Your advantages

- The cable clamps provide strain relief
- The halogen-free plastic troughs have been designed to be perfectly secure while simultaneously protecting the conductors
- Individual or bundled cables with a diameter of up to 38 mm can be installed safely and easily

Commercial data

Item number	3240258
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE7421
Product key	BE7421
Catalog page	Page 583 (C-3-2019)
GTIN	4046356464505
Weight per piece (including packing)	64 g
Weight per piece (excluding packing)	65.39 g
Customs tariff number	73269098
Country of origin	CN

WCC 38 - Cable clamp

3240258

<https://www.phoenixcontact.com/gb/products/3240258>




Technical data

Product properties

Product type	Cable feed-through
--------------	--------------------

Dimensions

Dimensional drawing	
Wrench size	10 mm
Wrench size for mounting	10 mm

Material specifications

Material	Steel
Coating	galvanized

Cable/line

External cable diameter	34 mm ... 38 mm
-------------------------	-----------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

WCC 38 - Cable clamp


3240258

<https://www.phoenixcontact.com/gb/products/3240258>



Drawings

Dimensional drawing



WCC 38 - Cable clamp

3240258

<https://www.phoenixcontact.com/gb/products/3240258>



Classifications

ECLASS

ECLASS-13.0	23159090
-------------	----------

ETIM

ETIM 9.0	EC011571
----------	----------

UNSPSC

UNSPSC 21.0	31162900
-------------	----------

WCC 38 - Cable clamp

3240258

<https://www.phoenixcontact.com/gb/products/3240258>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk