



Timing belt tools drawer t1a

3463-T1A

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:51:03





DESCRIPTION

Timing belt tools drawer t1a

Drawer T1 of the multi-marque timing setting tool trolley 3463-91N.
Approach tooling.

390cm extra-long female articulated 1/4" / 5/16" bit-holder ratchet.

390cm extra-long male articulated 1/4" / 3/8" square ratchet.

Extra-flat 1/4" / 3/8" ratchet.

Female Torx ratchet wrench E6+E8.

Set of 9 mixed articulated ratchet wrenches (8/10/11/12/13/14/15/16/17).

Telescopic magnet with mirror.

LED lamp.

Felt-tip for marking pulleys.

Scraper on handle with interchangeable blade.

Set of blades for scraper.

Set of six 1/4" 6-flat bits (3/4/5/6/7/8).

Set of seven 1/4" tamper-proof Torx bits (T15/T20/T25/T27/T30/T40).

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:51:03



- Set of four 1/4" XZN bits (M4/M5/M6/M8).
- Set of five 5/16" Torx bits (T30/T40/T45/T50/T55).
- Set of five 5/16" 6-flat bits (5/6/7/8/10).
- Set of four 5/16" XZN bits (M6/M8/M10/M12).
- Set of four 5/16" RIBE bits (M6/M8/M10/M12).
- 1/4" F and 1/4" F bit holder (bits).
- 3/8" F and 5/16" F bit holder (bits).
- 1/4" universal joint.
- 1/4" extension length 50 mm.
- 1/4" extension length 100 mm.
- 3/8" extension length 75 mm.
- Set of six 1/4" sockets (6/7/8/9/10/11).
- Set of ten short 3/8" sockets (10/11/12/13/14/15/16/17/18/19).
- Set of seven short 3/8" female Torx sockets, T6 to T16.
- Set of long 6-flat male keys with storage support.
- Set of long Torx wrenches with storage support.
- Stripping tool.
- Safety label.
- Drawer 1 empty foam module for approach tool 2018

SPECIFIC DATA

Designation	APPROACH TOOLS
Sales reference	3463-T1A
Weight (g)	4500
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

SAM Outillage













10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



Toolset

	x 1	Ratchet holder fittings 1/4" and 5/16" L.390 72135
	x 1	Square ratchet male 1/4" and 3/8" L.390 72136
	x 1	Ratchet 1/4" - 3/8" extra flat 72137
	x 1	Female ratchet wrench Torx® e6 + e8 217E6E8
	x 1	Set of 9 short articulated combination wrenches 2112-90
	x 1	Flexible magnet 2802
	x 1	LED lamp pen with cable P3462-237
	x 1	Felt pin pen to mark the pulley P3462-195
	x 1	Scraper for brake bleeder 37104... Ref : 371043
	x 1	Scraper blades for 37104... 371043-... Ref : 371043-16
	x 3	Set of 6 Torx® bits breath 240-... Ref : 240-490 - 240-590 - 240-3900
	x 4	Set of 5 Torx® bit 5/16 241-... Ref : 241-390 - 241-490 - 241-590 - 241-990

SAM Outillage














10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:51:03



	x 1	Bit holder 1/4" 19129N
	x 1	Bit holder 3/8" f and 5/16" f 19139N
	x 1	1/4" joint R-240
	x 2	Straight 1/4" extensions R-21... Ref : R-210 - R-211
	x 1	Straight 3/8" extensions J-2... Ref : J-208
	x 1	6-piece 1/4" socket set P3462-19120
	x 1	10-piece 3/8" socket set P3462-19130
	x 1	7-piece Torx® 3/8" socket set P3462-19134
	x 1	9 long hexagonal keys rack 244-90
	x 1	9 long Torx® keys rack 243-93
	x 1	Tool to empty P3462-71
	x 1	Security label P3462-99
	x 1	Empty foam module 3/3 for approach tools 2018 2903-T1A