

# C820 Woodruff Cutter Specification

Part NO.	Description	Material	Finish	Cut Length	Overall Length	No. of Flutes	Manf. Dia.	Shank Dia.
C820*10.5X2	Woodruff Keyseating	HSS	BRIGHT	2,0	57,0	6	10.5	6
C820*10.5X2	Woodruff Keyseating	HSS	BRIGHT	2,5	57,0	6	10.5	6
C820*10.5X3	Woodruff Keyseating	HSS	BRIGHT	3,0	57,0	6	10.5	6
C820*204	Woodruff Keyseating	HSS	BRIGHT	1/2	57,0	6	12.7	1/2
C820*304	Woodruff Keyseating	HSS	BRIGHT	1/2	57,0	6	12.7	1/2
C820*404	Woodruff Keyseating	HSS	BRIGHT	1/2	57,0	6	12.7	1/2
C820*13.5X2	Woodruff Keyseating	HSS	BRIGHT	2,0	57,0	6	13.5	12
C820*13.5X2	Woodruff Keyseating	HSS	BRIGHT	2,5	57,0	6	13.5	12
C820*13.5X3	Woodruff Keyseating	HSS	BRIGHT	3,0	57,0	6	13.5	12
C820*13.5X4	Woodruff Keyseating	HSS	BRIGHT	4,0	57,0	6	13.5	12
C820*305	Woodruff Keyseating	HSS	BRIGHT	5/8	57,0	6	15.88	1/2
C820*405	Woodruff Keyseating	HSS	BRIGHT	5/8	57,0	6	15.88	1/2
C820*505	Woodruff Keyseating	HSS	BRIGHT	5/8	57,0	6	15.88	1/2
C820*16.5X2	Woodruff Keyseating	HSS	BRIGHT	2,5	57,0	6	16.5	12
C820*16.5X3	Woodruff Keyseating	HSS	BRIGHT	3,0	57,0	6	16.5	12
C820*16.5X4	Woodruff Keyseating	HSS	BRIGHT	4,0	57,0	6	16.5	12
C820*16.5X5	Woodruff Keyseating	HSS	BRIGHT	5,0	57,0	6	16.5	12
C820*406	Woodruff Keyseating	HSS	BRIGHT	3/4	57,0	6	19.05	1/2
C820*506	Woodruff Keyseating	HSS	BRIGHT	3/4	57,0	6	19.05	1/2
C820*606	Woodruff Keyseating	HSS	BRIGHT	3/4	57,0	6	19.05	1/2
C820*19.5X3	Woodruff Keyseating	HSS	BRIGHT	3,0	57,0	6	19.5	12
C820*19.5X4	Woodruff Keyseating	HSS	BRIGHT	4,0	57,0	6	19.5	12
C820*19.5X5	Woodruff Keyseating	HSS	BRIGHT	5,0	57,0	6	19.5	12
C820*507	Woodruff Keyseating	HSS	BRIGHT	7/8	63,5	8	22.23	1/2
C820*607	Woodruff Keyseating	HSS	BRIGHT	7/8	63,5	8	22.23	1/2
C820*707	Woodruff Keyseating	HSS	BRIGHT	7/8	63,5	8	22.23	1/2
C820*807	Woodruff Keyseating	HSS	BRIGHT	7/8	63,5	8	22.23	1/2
C820*22.5X4	Woodruff Keyseating	HSS	BRIGHT	4,0	63,5	8	22.5	12
C820*22.5X5	Woodruff Keyseating	HSS	BRIGHT	5,0	63,5	8	22.5	12
C820*22.5X6	Woodruff Keyseating	HSS	BRIGHT	6,0	63,5	8	22.5	12
C820*608	Woodruff Keyseating	HSS	BRIGHT	1.	70,0	8	25.4	1/2
C820*708	Woodruff Keyseating	HSS	BRIGHT	1.	70,0	8	25.4	1/2
C820*808	Woodruff Keyseating	HSS	BRIGHT	1.	70,0	8	25.4	1/2
C820*1008	Woodruff Keyseating	HSS	BRIGHT	1.	70,0	8	25.4	1/2
C820*25.5X5	Woodruff Keyseating	HSS	BRIGHT	5,0	70,0	8	25.5	12
C820*25.5X6	Woodruff Keyseating	HSS	BRIGHT	6,0	70,0	8	25.5	12
C820*25.5X7	Woodruff Keyseating	HSS	BRIGHT	7,0	70,0	8	25.5	12
C820*25.5X8	Woodruff Keyseating	HSS	BRIGHT	8,0	70,0	8	25.5	12
C820*28.5X5	Woodruff Keyseating	HSS	BRIGHT	5,0	70,0	8	28.5	12
C820*28.5X6	Woodruff Keyseating	HSS	BRIGHT	6,0	70,0	8	28.5	12
C820*28.5X7	Woodruff Keyseating	HSS	BRIGHT	7,0	70,0	8	28.5	12
C820*28.5X8	Woodruff Keyseating	HSS	BRIGHT	8,0	70,0	8	28.5	12
C820*609	Woodruff Keyseating	HSS	BRIGHT	1.1/8	70,0	8	28.58	1/2
C820*709	Woodruff Keyseating	HSS	BRIGHT	1.1/8	70,0	8	28.58	1/2
C820*809	Woodruff Keyseating	HSS	BRIGHT	1.1/8	70,0	8	28.58	1/2
C820*1009	Woodruff Keyseating	HSS	BRIGHT	1.1/8	70,0	8	28.58	1/2
C820*610	Woodruff Keyseating	HSS	BRIGHT	1.1/4	70,0	8	31.75	1/2
C820*710	Woodruff Keyseating	HSS	BRIGHT	1.1/4	70,0	8	31.75	1/2
C820*810	Woodruff Keyseating	HSS	BRIGHT	1.1/4	70,0	8	31.75	1/2

# C820 Woodruff Cutter Specification

Part NO.	Description	Material	Finish	Cut Length	Overall Length	No. of Flutes	Manf. Dia.	Shank Dia.
C820*1010	Woodruff Keyseating	HSS	BRIGHT	1.1/4	70,0	8	31.75	1/2
C820*1210	Woodruff Keyseating	HSS	BRIGHT	1.1/4	70,0	8	31.75	1/2
C820*32.5X5	Woodruff Keyseating	HSS	BRIGHT	5,0	70,0	10	32.5	12
C820*32.5X6	Woodruff Keyseating	HSS	BRIGHT	6,0	70,0	10	32.5	12
C820*32.5X7	Woodruff Keyseating	HSS	BRIGHT	7,0	70,0	10	32.5	12
C820*32.5X8	Woodruff Keyseating	HSS	BRIGHT	8,0	70,0	10	32.5	12
C820*811	Woodruff Keyseating	HSS	BRIGHT	1.3/8	76,0	10	34.92	1/2
C820*1011	Woodruff Keyseating	HSS	BRIGHT	1.3/8	76,0	10	34.92	1/2
C820*1211	Woodruff Keyseating	HSS	BRIGHT	1.3/8	76,0	10	34.92	1/2
C820*35.5X6	Woodruff Keyseating	HSS	BRIGHT	6,0	76,0	10	35.5	12
C820*35.5X7	Woodruff Keyseating	HSS	BRIGHT	7,0	76,0	10	35.5	12
C820*35.5X8	Woodruff Keyseating	HSS	BRIGHT	8,0	76,0	10	35.5	12
C820*35.5X9	Woodruff Keyseating	HSS	BRIGHT	9,0	76,0	10	35.5	12
C820*812	Woodruff Keyseating	HSS	BRIGHT	1.1/2	76,0	10	38.1	1/2
C820*1012	Woodruff Keyseating	HSS	BRIGHT	1.1/2	76,0	10	38.1	1/2
C820*1212	Woodruff Keyseating	HSS	BRIGHT	1.1/2	76,0	10	38.1	1/2
C820*38.5X7	Woodruff Keyseating	HSS	BRIGHT	7,0	76,0	10	38.5	12
C820*38.5X8	Woodruff Keyseating	HSS	BRIGHT	8,0	76,0	10	38.5	12
C820*38.5X9	Woodruff Keyseating	HSS	BRIGHT	9,0	76,0	10	38.5	12
C820*38.5X1	Woodruff Keyseating	HSS	BRIGHT	10,0	76,0	10	38.5	12
C820*45.5X1	Woodruff Keyseating	HSS	BRIGHT	10,0	76,0	12	45.5	12