



Power Jet-Light ELP 55 IP 54 Strahler

Für den Außen- und Innenbereich.

- Perfekt für den gewerblichen Einsatz und den anspruchsvollen Heimwerker.
- Elektronisches Vorschaltgerät für hohe Energieeffizienz, flackerfreies Licht und geringe Erwärmung.
- Starke Leuchtkraft.
- Steckdosen spritzwassergeschützt, mit selbstschließenden Deckeln.
- Ein/Aus Schalter für Licht.
- Bruch- und schlagfestes Kunststoffgehäuse.
- Mit ausklappbarem, verstellbarem Haltebügel zum Aufstellen oder Befestigen auf einem Stativ.
- Neopren-Gummianschlussleitung mit Schutzkontakt-Stecker.
- Inklusive 55 W Leuchtmittel.
- Im farbigen Verkaufs-Karton.
- Steckdosen: 2 x 230 V
- Wirkungsgrad Vorschaltgerät: A3
- Energieeffizienzklasse: B

Power Jet-Light ELP 55 IP 54 spotlight

For use indoors and outdoors.

- Perfect for tradesmen and advanced DIY workers.
- Electronic ballast for energy efficiency, flicker-free light and minimum heat output.
- Very bright light.
- Water-jet protected socket outlets with self-closing protective caps.
- ON/OFF switch.
- Break and impact resistant plastic housing.
- Adjustable folding stand, also suitable for mounting on a tripod.
- With special rubber cable and water-jet protected earthed plug.
- 55 W bulb included.
- In colourful display-packaging.
- Sockets: 2 x 230 V
- Ballast efficiency: A3
- Energy efficiency class: B



Artikel-Nr. Article No.	Barcode 4007123...	VPE UP	Kabellänge Cable length	Kabelbezeichnung Cable	Leistung Output	Lichtstrom Luminous flux	Wirkungsgrad Lampe Lamp efficacy	Farbtemperatur Colour temperature	Fassung Fittings
1 17272 0	592579	1	1,8 m	H07RN-F 3G1,5	55 W	3600 lm	66 lm/W	6400 K	GR10q
1 17272 0 005	610037	1	5 m	H07RN-F 3G1,5	55 W	3600 lm	66 lm/W	6400 K	GR10q

Empfohlenes Zubehör: / Recommended accessories:

Artikel-Nr. Article No.	Barcode 4007123...	VPE UP	Bezeichnung Description	Tragfähigkeit Loading capacity	Höhenverstellbar Height-adjustable
1 17061 0	190614	1	Bau-Teleskop Stativ BS 250 / Building Telescope Tripod BS 250	7 kg	max. 2,5 m

Artikel-Nr. Article No.	Barcode 4007123...	VPE UP	Bezeichnung Description	Leistung Output	Lichtstrom Luminous flux	Wirkungsgrad Lampe Lamp efficacy	Farbtemperatur Colour temperature	Farbwiedergabeindex Colour rendering index	Fassung Fittings
1 17272 0	210206	1	Jet-Light-Leuchtmittel/bulb	55 W	3600 lm	66 lm/W	6400 K	80	GR10q