



DELTA style, SCHUKO socket outlet 10/16 A 250 V Green bezel (SV)  
cover plate 68 x 68 mm

Model	
product brand name	DELTA
product designation	SCHUKO socket outlet
cover version	central plate
design of the special power supply unit	without special current supply
design of the socket / according to VDE 0620 for severe conditions	No
design of the phase tap	No
General technical data	
marking / of socket outlet	without imprint
mounting type	fixing with claw and screw
surface processing	others
material	thermoplastic
Supply voltage	
operating voltage / rated value	250 V
Protection class	
protection class IP	IP20
Main circuit	
operational current / rated value	16 A
Appearance	
color	green
Product details	
product component	
<ul style="list-style-type: none"> <li>• ejection equipment</li> <li>• labeling field</li> <li>• increased touch protection</li> <li>• residual current device</li> <li>• miniature fuse</li> <li>• integrated / functional lighting</li> <li>• integrated / light source</li> <li>• integrated / orientation lighting</li> <li>• hinged lid</li> </ul>	<ul style="list-style-type: none"> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> </ul>
product feature	
<ul style="list-style-type: none"> <li>• lockable</li> <li>• halogen-free</li> <li>• transparent</li> </ul>	<ul style="list-style-type: none"> <li>No</li> <li>Yes</li> <li>No</li> </ul>
Product function	

product function		
• socket selectable	No	
• overvoltage protection	No	
<b>Number</b>		
number of units	1	
number of sockets / switchable	0	
<b>Connections</b>		
arrangement of contacts / diagonal	No	
type of electrical connection	plug terminal	
<b>Mechanical Design</b>		
height	70 mm	
width	70 mm	
depth	45 mm	
fastening method	flush mounted	
material / of the enclosure	plastic	
<b>General Product Approval</b>	<b>Declaration of Conformity</b>	<b>Test Certificates</b>



[Type Test Certificates/Test Report](#)

[Miscellaneous](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=5UB1851>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5UB1851>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=5UB1851](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=5UB1851)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

