



# tesa<sup>®</sup> PRO 66965

## Mounting Transparent

### Product Information

tesa PRO Mounting Transparent - Durable, crystal clear and extra thin adhesive mounting tape, double-sided - Ideal for most indoor and outdoor use

### Product Description

tesa PRO Mounting Transparent

Attach flat objects both in indoor and outdoor spaces: Use on surfaces, such as glass, tiles, finished wood and many types of plastic. The crystal clear and extra thin tape can resist temperatures up to 100°C. It is resistant to damage caused by moisture, (certain) chemicals, softening agents and UV-light. A single 10 cm strip can hold up to 2 kg. It's the perfect solution for mounting items on transparent and solid surfaces.

Apply in vertical strips and along the full length of the object or surface. Press down firmly on the mounting tape for at least five seconds.

### Product Features

\*Strong and durable: temperature-resistant up to 100°C in the long term, resistant to damage caused by moisture, (certain) chemicals, softening agents and UV-light

\*Works almost invisible: the transparent tape adheres to smooth surfaces like glass, tiles, wood and various types of plastics

\*Ideal for interior and exterior use: Strong double-sided adhesive tape for secure fixing of flat objects such as signs, thermometers and more

\*Easy to use: The mounting tape can be cut into individual small or large pieces for an adhesive strip in the optimized size

\*Scope of delivery: 1 x tesa PRO Mounting Transparent - Holds up to 2 kg per 10 cm tape - Material: Tackified acrylic

### Application Fields

Easy to apply:

- In order for the mounting tape to develop its full holding power, the object and surface must be free of dust, dirt and grease
- Attach to the rougher surface first
- Apply in vertical strips and along the full length of the object or surface.
- Press down firmly for at least five seconds
- For removal, carefully pull the mounting tape parallel from the wall. As the mounting tapes are intended for permanent use, material residues may remain on the object. Try to remove with tesa adhesive remover.



# tesa<sup>®</sup> PRO 66965

## Mounting Transparent

### Product Information

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

### Product Construction

- |                    |                   |                   |        |
|--------------------|-------------------|-------------------|--------|
| • Backing material | PET film          | • Total thickness | 205 µm |
| • Type of adhesive | tackified acrylic |                   |        |

### Properties/Performance Values

- |                          |           |                       |           |
|--------------------------|-----------|-----------------------|-----------|
| • Tensile strength       | 20 N/cm   | • Chemical resistance | good      |
| • Ageing resistance (UV) | very good | • Humidity resistance | very good |

### Disclaimer

tesa<sup>®</sup> products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa<sup>®</sup> product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?mp=66965>