



PRODUCT-DETAILS

TVOC-2-DP15

TVOC-2-DP15 Detector



概要信息	
产品型号	TVOC-2-DP15
产品ID	1SFA664003R1150
欧洲商品编号(EAN)	7320500382325
目录说明	TVOC-2-DP15 Detector
详细描述	The TVOC-2-DP15 Detector Cable 15 m is a key accessory to the TVOC-2 Arc Guard System. The detectors are installed in the switchgear panels to monitor for any unwanted arc flashes. The detectors consists of a fiber optic cable connected to a lens that can detect light in a 180 degree angle at distances of 3 m, depending on the light intensity.

Material Compliance	
REACH Declaration	2AGS2022-006202
RoHS信息	2AGS2022-006277-RoHS
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT001035D0902a

环境条件	
周围环境温度	Operation -25 ... +70 °C Storage -25 ... +85 °C
环境信息	1SFC170003D0201

订货信息	
当地订购代码_USCON	TVOC-2-DP15
E-Number (Finland)	2712010
E-Number (Norway)	4116466
E-Number (Sweden)	2801721
欧洲商品编号(EAN)	7320500382325
最小起订量	1 piece
海关关税号	85389099

尺寸	
产品净宽	350 mm
产品净高	20 mm
产品净深	300 mm
产品净重	0.15 kg

包装信息	
1级包装单元	bag 1 piece
1级包装宽度	300 mm
1级包装高度	20 mm
1级包装长度	350 mm
1级包装 总重	0.15 kg
1级包装 EAN	7320500382325

其他信息	
其它信息	DETECTOR suitable for TVOC-2
产品系列	TVOC-2
产品	Detector
适用于	TVOC-2
适用产品系列	Arc Monitor

技术参数	
安装类型	Connected to main unit or extension module
辅助触点CO (SPDT)数量	0
辅助触点NC数量	0
辅助触点NO数量	0

认证及声明（文件编码）	
BV认证	39407_B1
CSA 认证	UL_20110511-E155370

cULus 认证	UL_20110511-E155370
数据手册, 技术资料	1SFC170001C0201
符合性声明 - CE	2CMT005420
DNV认证	DNV_E-12926
EAC认证	9AKK106713A1450
UL认证	UL_20110511-E155370
说明书和手册	1SFC170011M0201
说明书和手册 (第2部分)	1SFC170011M0201

分类

ETIM 8	EC002911 - Arc detection system
ETIM 9	EC002911 - Arc detection and mitigation system
IDEA 粒度分类代码 (IGCC)	6958 >> Fiber optic detector
对象分类代码	B
UNSPSC	43223319
WEEE 类别	Product Not in WEEE Scope
e级	V11.0 : 27142214

分类

低压产品及系统 → 断路器类产品 → External Digital Unit → Arc Guard System
中压产品与系统 → 服务业务 → 备件 → Parts → All Spare Parts (Relays-SWG-CB)

