

Product datasheet

Specifications



PANEL KIT CLASS 2 TARIF METERING 3P W300

LVS03142

EAN Code: 3606481866196

Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Metering panel kit
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G duct
Type of front plate	Cut-out
Installed device	Resi9: by screws DB 90 - control: toggle - vertical installation Power meters: kilowatt-hour meters - vertical installation
Poles description	1 x 1P + N: mounting plate support: DB 90 vertical installation 1 x 3P + N: mounting plate support: kilowatt-hour meters vertical installation

Complementary

Enclosure/cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Number of vertical modules [50 mm]	13
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	650 mm
Width	300 mm
Net weight	4.92 kg
Quantity per set	Set of 1
functional unit	300 mm PrismaSeT G floor-standing duct Resi9 DB 90 by screws toggle vertical 1P + N 1 12 50 mm 300 mm PrismaSeT G wall-mounted duct Resi9 DB 90 by screws toggle vertical 1P + N 1 12 50 mm 300 mm PrismaSeT G floor-standing duct power meters kilowatt-hour meters vertical 3P + N 1 12 50 mm 300 mm PrismaSeT G wall-mounted duct power meters kilowatt-hour meters vertical 3P + N 1 12 50 mm

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	11.0 cm
------------------	---------

Package 1 Width	28.0 cm
-----------------	---------

Package 1 Length	62.0 cm
------------------	---------

Package 1 Weight	4.478 kg
------------------	----------

Unit Type of Package 2	P12
------------------------	-----

Number of Units in Package 2	16
------------------------------	----

Package 2 Height	58.0 cm
------------------	---------

Package 2 Width	80.0 cm
-----------------	---------

Package 2 Length	120.0 cm
------------------	----------

Package 2 Weight	83.648 kg
------------------	-----------

Contractual warranty

Warranty (in months)	18
----------------------	----


Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.


[Environmental Data explained >](#)

[How we assess product sustainability >](#)


Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
Halogen-free status	Halogen free plastic parts product
PVC free	Yes
Silicone-free	Yes

Use Longer

 Lifetime extension	
Repair	No

Use Again

 Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No