



**Part Number :** [1731120228](#)

**Product Description :** FCT Machined Contact, Female, Crimp, 1.30µm Gold Plating, Split Tine, 28-22 AWG, 500 Pieces

**Series Number :** 173112

**Status :** Active

**Product Category :** D-Sub Contacts

**Engineering Number :** FK22SL-13V-5783



---

## Documents & Resources

### Drawings

[1731120228 sd.pdf](#)

### Specifications

[2195600650-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT Machined Contact, Female, Crimp, 1.30µm Gold Plating, Split Tine, 28-22 AWG, 500 Pieces
Contact Type	Machined Crimp
Magnetic	Yes
Product Name	FCT Products
Type	High Density
UPC	889056489836

### Electrical

Current - Maximum per Contact	5.0A
-------------------------------	------

### Physical

Durability (mating cycles min)	500
Gender	Female
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Gold over Nickel
Net Weight	0.200/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	1.300µm
Plating min - Termination	1.300µm
Temperature Range - Operating	-55° to +130°C

Termination Style	Crimp
Wire Size (AWG)	22, 24, 26, 28

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Use With	FCT High-Density Connectors

---

## Application Tooling

### Global

Description	Part Number
FCT Hand Crimp Tool, Mini Frame, 8-Step Adjust	<a href="#"><u>1731121730</u></a>
FCT Locator for Size 22 Contacts, Socket	<a href="#"><u>1731121737</u></a>
FCT Installation and Removal Tool for High-Density Contacts	<a href="#"><u>1731121745</u></a>
FCT Installation and Removal Tool for High-Density Contacts	<a href="#"><u>1731121746</u></a>