

22MM METAL ROUND ACTUATOR: SELECTOR SWITCH
LONG HANDLE RIGHT LATCH.,LE.MOMEN.CONT.TYPE 3
SWITCH POSITIONS I-O-II NON-ILLUMINATED WITH
HOLDER WHITE

Actuator:

Design of the operating mechanism		selector switch with 3 switch positions
Shape / of the activation element		round
Manner of function / of the activation element		Yes
• arresting lock • tentative		Yes
Outer diameter / of the activation element	mm	28.5
Material / of the activation element		plastic

Button:

Color / of the button		white
-----------------------	--	-------

Front ring:

Material / of the front ring		metal
Color / of the front ring		silver

General technical details:

Design of the product		with 3 switch positions
Number of control points		1
Number of indicator lights / installable		0
Number of switching positions		3
Product extension / optional / fluorescent materials		No
Product function / emergency-OFF function		No
Type of unlocking device		rotate-to-unlatch mechanism
Resistance against shock		<= 50g
• for devices without incandescent lamp / according to IEC 60068-2-27		
Operating cycles / maximum	1/h	1,000
Resistance against vibration / according to IEC 60068-2-6		20 ... 200 Hz: 5g
Mechanical operating cycles as operating time / typical		300,000
Item designation		S
• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		

- according to DIN EN 61346-2

S

Auxiliary Contacts:

Number of NC contacts / for auxiliary contact	0
Number of NO contacts / for auxiliary contact	0
Number of change-over switches / for auxiliary contact	0

Installation/mounting/dimensions:

Product component / front ring	Yes
Material / of the housing	metal
Type of mounting	front mounting
Installation width	mm 22
Shape / of the installation hole	round
Mounting diameter	mm 22
Height	mm 30
Width	mm 30
Depth	mm 53
Tightening torque / of the screws in the holder / maximum	N·m 1

Ambient conditions:

Ambient temperature		
• during the operating phase	°C	70 ... -25
• during storage	°C	-40 ... 80
Protection class IP		IP67
Climatic class / according to DIN EN ISO 6270-2		KTW24

Certificates/approvals:

General Product Approval



Test Certificates

[Manufacturer](#)

Shipping Approval

[ABS](#)



[PRS](#)



other

[Manufacturer](#)


Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>



last change:

Sep 6, 2010