

1" IMPACT CR-MO SOCKET SET WITH CASE DIN 27-50MM



- Chrome molybdenum composition providing superior tensile strength and elasticity, perfect for high-torque tasks
- 8 regular 6-point metric sockets in sizes 27, 30, 32, 36, 38, 41, 46, and 50 mm ensure that you are prepared for demanding tasks
- Included Cr-Mo step-up adapter 3/4" F x 1" M along with retaining pins and rubber rings allows for smooth and secure socket attachment when switching between different tool sizes
- Comes in a durable TengTools metal carrying case for storage and easy transportation
- Performance at least in accordance with DIN 3129 for mechanical specifications and power tool compatibility

This 13-piece TengTools 1" impact socket set is an indispensable tool for the mechanical needs of professional maintenance teams, heavy equipment mechanics, and construction engineers. The set is made to meet DIN 3129 standards, crafted from Chrome Molybdenum (Cr-Mo) and includes a range of 8 sizes from 27 to 50 mm. Designed for use with power tools, the assortment of socket sizes and high-torque compatibility make this robust set perfect for industrial assembly lines or maintaining heavy machinery.

General information

Country of origin: Taiwan
Barcode: 5020385020498
Tariff code Europe: 8204200000
ECCN US: EAR99
UNSPSC: 27111703

Dimensions

Net weight (g): 9050
Width (mm): 420
Depth (mm): 125
Height (mm): 78

Attributes

Product type: Impact Tool Sets, Socket Sets, Impact Sockets
Number of pieces: 13
Drive: 1"
Socket type: Regular, 6-point
Standard type: DIN
Unit of measurement: Metric

Technical changes and errors may occur. 01-08-2024 19:59



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
 441 39 Alingsås, Sweden

LIST OF CONTENTS



9113 1" Impact Cr-Mo socket set with case DIN 27-50 mm

910527 1" Impact Socket DIN Metric 27 mm

910530 1" Impact Socket DIN Metric 30 mm

910532 1" Impact Socket DIN Metric 32 mm

910536 1" Impact Socket DIN Metric 36 mm

910538 1" Impact Socket DIN Metric 38 mm

910541 1" Impact Socket DIN Metric 41 mm

910546 1" Impact Socket DIN Metric 46 mm

910550 1" Impact Socket DIN Metric 50 mm

940085-C Impact Step Up Adaptor 3/4"F - 1"M DIN

O95036 Retaining Ring 36 x 5.0 mm

O97045 Retaining Ring 45 x 7.0 mm

P90435 Retaining Pin 4 x 35 mm

P90545 Retaining Pin 5 x 45 mm