

Product type designation

Product description

PB FC M12 Plug PRO

M12 connector with pin insert, 4-pole, B-coded
PB FC M12 PLUG PRO M12 PLUG CONNECTOR WITH RUGGED METAL HOUSING AND FC CONNECTING METHOD, WITH AXIAL CABLE OUTLET, FOR USE WITH ET200PRO, PIN CONNECTOR, (B CODED) PACKAGING UNIT 5 PIECES



Suitability for use

For connecting electrical PB FC bus cables to ET200 PRO, suitable for fast assembly with the FastConnect system

Transmission rate

Transfer rate / with PROFIBUS

9.6 kbit/s ... 12 Mbit/s

Interfaces

Number of electrical connections

- for PROFIBUS cables
- for network components or terminal equipment

1
1

Type of electrical connection

- for PROFIBUS cables
- for network components or terminal equipment

Integrated insulation displacement contacts for 2-core PB FC installation cables
M12 connector (male insert, 4-pin, B-coded)

Type of electrical connection / FastConnect

Yes

Mechanical data

Material / of the enclosure

metal

Number of reuses

10

Design, dimensions and weight

Type of cable outlet

180° cable outlet

Width

19 mm

Height

19 mm

Depth

73 mm

Net weight

40 g

Permitted ambient conditions	
Ambient temperature	
<ul style="list-style-type: none"> during operation 	-40 ... +85 °C
<ul style="list-style-type: none"> during storage 	-40 ... +85 °C
<ul style="list-style-type: none"> during transport 	-40 ... +85 °C
Chemical resistance / to water	resistant
Protection class IP	IP65/67

Product properties, functions, components / general	
Product property	
<ul style="list-style-type: none"> silicon-free 	Yes
Product component	
<ul style="list-style-type: none"> strain relief 	Yes

Standards, specifications, approvals	
Certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes
<ul style="list-style-type: none"> UL approval 	Yes
<ul style="list-style-type: none"> cULus approval 	Yes
<ul style="list-style-type: none"> Railway application in accordance with EN 50155 	No

Further Information / Internet Links	
Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL 	http://www.siemens.com/snst
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/automation/net/catalog
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAx Download Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com
last modified:	07.05.2015