

Features

- Engineered for precise cutting of thin-wall metal pipes and closed profiles.
- Manufactured from fully hardened, high-grade High-Speed Steel (HSS), it features a very fine 1.2mm tooth pitch and a long 132mm blade length, making it ideal for cutting pipes and profiles with wall thicknesses of 1–3mm and diameters up to 65mm.

Jigsaw Blade –Metal T318A –Standard Cut

RS Stock No.: 0757839



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Jigsaw Blade

0757839 Standard for Metal Jigsaw Blade is engineered for precise cutting of thin-wall metal pipes and closed profiles. Manufactured from fully hardened, high-grade High-Speed Steel (HSS), it features a very fine 1.2mm tooth pitch and a long 132mm blade length, making it ideal for cutting pipes and profiles with wall thicknesses of 1–3mm and diameters up to 65mm.

- *Wavy Set Teeth for fine, straight cutting*
- *Suitable for use on Mild Steel, Sheet Steel, High Grade Steel & Steel Pipes*
- *Bayonet (T-Shank) fitting system compatible with all popular brands of bayonet fitting machines*
- *Supplied in 5pc Packs*

General Specifications

Tooth Design	Wavy Set, Milled
Type	Jigsaw Blade
Teeth Spacing	1.2mm
Cut Depth	<65mm
Cut Type	Standard Cutting
Material	High Speed Steel
Fitting	Bayonet (T-Shank)
Length	132mm

Stock No.	Cut Type	Teeth Spacing	Length	Tooth Design
XXX-XXXX 0757836	Standard Cutting	1.1–1.5mm	77mm	Wavy Set, Milled
XXX-XXXX 0757837	Standard Cutting	1.9–2.3mm	77mm	Wavy Set, Milled
XXX-XXXX 0757838	Standard Cutting	0.7mm	77mm	Wavy Set, Milled
XXX-XXXX 0757839	Standard Cutting	1.2mm	132mm	Wavy Set, Milled
XXX-XXXX 0757840	Standard Cutting	2.0mm	132mm	Wavy Set, Milled
XXX-XXXX 0757842	Special Cutting	3.0mm	100mm	Side Set, Milled

Approvals

Declarations	REACH DoC
---------------------	-----------

Similar Products

Stock No.	Brand	Product Name	Cut Type	Teeth Spacing	Length	Tooth Design
XXX-XXXX 0757836	RS PRO	Jigsaw Blade	Standard Cutting	1.1-1.5mm	77mm	Wavy Set, Milled
XXX-XXXX 0757837	RS PRO	Jigsaw Blade	Standard Cutting	1.9-2.3mm	77mm	Wavy Set, Milled
XXX-XXXX 0757838	RS PRO	Jigsaw Blade	Standard Cutting	0.7mm	77mm	Wavy Set, Milled
XXX-XXXX 0757839	RS PRO	Jigsaw Blade	Standard Cutting	1.2mm	132mm	Wavy Set, Milled
XXX-XXXX 0757840	RS PRO	Jigsaw Blade	Standard Cutting	2.0mm	132mm	Wavy Set, Milled
XXX-XXXX 0757842	RS PRO	Jigsaw Blade	Special Cutting	3.0mm	100mm	Side Set, Milled

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories