

Nevada

Medium weight cut resistant sleeves


Skytec Nevada sleeves offer comprehensive cut resistance. Rated to EN388 cut C/ANSI Cut A3, these breathable sleeves are available in two lengths & are designed to protect not only your arm but your wrist too thanks to the integrated thumbhole.

Features

- ▲ Cut resistant: Level C / ANSI A3
- ▲ Thumbhole prevents slipping & wrist exposure
- ▲ Gives increased protection from cuts, slash, tear & punctures
- ▲ Machine knitted double-ply medium weight sleeve
- ▲ Comfortable & protective, the seamless knitted liner avoids skin irritation & is elasticated for extra protection
- ▲ Resistance to contact heat up to 250°C
- ▲ Machine washable
- ▲ Available in two lengths - 14", 18"



Certifications



Suitable industries & applications

Industries

- ▲ Aerospace
- ▲ Automotive
- ▲ Manufacturing
- ▲ Chemicals
- ▲ Waste and Recycling
- ▲ Steel and Metals

Applications

- ▲ Metal Fabrication Work
- ▲ Handling Sharp or Abrasive Materials
- ▲ General Maintenance

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Nevada

Medium weight cut resistant sleeves


Product information

Materials	Liner:	Para-Aramid
	Coating:	Uncoated
Colour	Yellow	
Cuff Style	Elasticated	

Ordering information


Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.