

# Wiha SYSTEM 6.

The compact allrounder.



Colour-coded ChromTop® tips for maximum clarity.


Are you looking for a versatile and compact tool system for your toolcase or for use on the road? Then our **SYSTEM 6** system with its 6 mm reversible blades and corresponding handles is the right solution for you. Just choose the right variation from the large selection of handles and reversible blades or decide on one of the **SYSTEM 6** sets.

- The **Starter Sets** in the robust roll-up bag are already equipped with the most commonly used reversible blades and offer space for a max. of 11 additional reversible blades.
- The **Professional Sets** are the perfect solution if you are looking for a professional, high-quality universal set in a rugged metal box.
- The practical sets in **roll-up pouches** are especially handy and compact.

The **Wiha SYSTEM 6** reversible blade systems are high-quality, industrial quality products, made with state-of-the-art materials and finished to the highest standard of workmanship. The 150 mm long reversible blades are made of high-quality chrome-vanadium-molybdenum steel, are through-hardened and chrome-plated. The various handles are especially ergonomically designed and guarantee optimal force-transmission. The **Wiha SYSTEM 6** system provides the right tool for every application – ideal for industry, trade and the ambitious handyman.



The Wiha SYSTEM 6 range is the compact allrounder for different applications.



The SoftFinish® telescopic handle with ClickStop ball clamping for a secure hold and rapid blade change.

## Wiha SYSTEM 6.

- Flexible, versatile reversible-blade system in industrial quality
- Expandable individual tool system
- Ergonomic handles for almost every application
- Colour-coded blades made of high-quality, tough chrome-vanadium-molybdenum steel, through-hardened, chrome-plated
- Wiha ChromTop® tips ensure a perfect fit every time

### SYSTEM 6 handles.



**284** SYSTEM 6 SoftFinish®-telescopic handle.  
Ergonomic multi-component handle with roll-off protection.  
Handle: With 6 mm hex retainer.  
Enables adjustable blade lengths from 42 - 114 mm.  
ClickStop ball clamp guarantees a secure hold and rapid blade exchange.  
Application: Versatile for general applications in the workshop and factory.

Order-No.	6.0	115	36	5
30372 3				



**SB 284** SYSTEM 6 SoftFinish®-telescopic handle.  
Blister packed.

Order-No.	6.0	122	36	1
30404 1				



**284ESD** SYSTEM 6 SoftFinish®-telescopic ESD handle.  
Dissipative handle, ESD-safe.  
Handle: Ergonomic multi-component handle with roll-off protection.  
With 6 mm hex retainer.  
Enables adjustable blade lengths from 42 - 114 mm.  
ClickStop ball clamp guarantees a secure hold and rapid blade exchange.  
Surface resistance  $10^6 - 10^9$  ohms.  
Standards: IEC 61340-5-1.  
Application: For working on electrostatically sensitive components.

Order-No.	6.0	115	36	5
31496 5				

**Safety Notice:**  
Wiha ESD screwdrivers are non-insulated, therefore not suitable for working on live parts.

### SYSTEM 6 handles.



**481 M01** SYSTEM 6 Magnetic handle.  
With built-in magnetiser/ demagnetiser.  
Handle: With built-in magnetiser/ demagnetiser.  
With hex bolster for additional torque.  
Use in combination with SYSTEM 6 reversible blades.  
Application: For magnetising/ demagnetising SYSTEM 6 reversible blades.

Order-No.	6.0	110	33	5
27625 6				



**282** SYSTEM 6 Topra ratchet.  
For all SYSTEM 6 reversible blades and 1/4" bits.  
Handle: With anti-clockwise rotation, clockwise rotation and locked position.  
Application: For best user comfort and high torque transfer.

Order-No.	6.0	100	85	5
03767 3				



**Press sleeve:**  
=> Blade locking is released



**Press and hold down sleeve:**  
=> Set desired blade length



**Release sleeve:**  
=> Blade is held securely

# Wiha SYSTEM 6.

The compact allrounder.

## SYSTEM 6 reversible blades.



### 284 SYSTEM 6 slotted reversible blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Order-No.	⌀	⌀	⊖	⊖	↔	⦿	⦿
27627 0	3.5	4.5	0.6	0.8	150	6.0	5
00629 7	4.0	6.0	0.8	1.0	150	6.0	5
00630 3	5.5	6.5	1.0	1.2	150	6.0	5



### 284 SYSTEM 6 combined slotted-Phillips reversible blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Order-No.	⌀	⊕	⊖	↔	⦿	⦿
00665 5	4.0	PH1	0.8	150	6.0	5
00666 2	6.0	PH2	1.0	150	6.0	5
00667 9	6.5	PH3	1.2	150	6.0	5



### 284 SYSTEM 6 Phillips reversible blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Order-No.	⊕	⊕	↔	⦿	⦿
00631 0	PH1	PH2	150	6.0	5
27628 7	PH2	PH3	150	6.0	5



### 284 SYSTEM 6 Pozidriv reversible blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Order-No.	⊕	⊕	↔	⦿	⦿
00632 7	PZ1	PZ2	150	6.0	5
27629 4	PZ2	PZ3	150	6.0	5

## SYSTEM 6 reversible blades.



### 284 SYSTEM 6 combined ball end hex - hex reversible blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Extra: The ball end enables the user to work at angles up to 25°.

Order-No.	⦿	⦿	↔	⦿	⦿
00635 8	2.5	2.5	150	6.0	5
00636 5	3	3	150	6.0	5
00637 2	4	4	150	6.0	5
00638 9	5	5	150	6.0	5
00639 6	6	6	150	6.0	5



### 284 SYSTEM 6 TORX® reversible blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Order-No.	⦿	⦿	↔	⦿	⦿
00654 9	T6	T8	150	6.0	5
00655 6	T7	T9	150	6.0	5
00656 3	T10	T15	150	6.0	5
00657 0	T20	T25	150	6.0	5
00658 7	T30	T40	150	6.0	5



### 284 SYSTEM 6 TORX® Tamper Resistant reversible blade.

For TORX® screws with locking pin.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips. With borehole in the blade tip.

Order-No.	⦿	⦿	↔	⦿	⦿
27630 0	T6H	T8H	150	6.0	5
27631 7	T7H	T9H	150	6.0	5
27632 4	T10H	T15H	150	6.0	5
27633 1	T20H	T25H	150	6.0	5
27634 8	T30H	T40H	150	6.0	5

## SYSTEM 6 reversible blades.



### 284 SYSTEM 6 Tri-Wing® reversible blade.

For Tri-Wing® security screws.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Order-No.	⦿	⦿	↔	⦿	⦿
27637 9	TW0	TW1	150	6.0	5
27638 6	TW2	TW3	150	6.0	5
27639 3	TW4	TW5	150	6.0	5



### 284 SYSTEM 6 Torq-Set® reversible blade.

For Torq-Set® security screws.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Order-No.	⊕	⊕	↔	⦿	⦿
27635 5	TS2	TS4	150	6.0	5
27636 2	TS6	TS8	150	6.0	5

## SYSTEM 6 reversible blades.



### 7802 SYSTEM 6 bit holder.

Suitable for C 6.3 and E 6.3 (1/4") bits.

Blade: Chrome-vanadium steel, through hardened, chrome-plated. Bit retainer made of stainless steel with integrated permanent magnet.

Order-No.	⦿	↔	⦿	⦿	⦿
03882 3	1/4	164	6.0	10	5



### 7803 SYSTEM 6 adapter blade.

Suitable for 1/4" square sockets.

Blade: Chrome-vanadium steel, through hardened, chrome-plated. 1/4" square drive with ball retainer.

Order-No.	⦿	↔	⦿	⦿	⦿
03883 0	1/4	164	6.0		5




### U109 00 SYSTEM 6 extension blade.

Suitable for blades.

Blade: Chrome-vanadium steel, through hardened, chrome-plated. Extends all SYSTEM 6 blades up to 100 mm.

Order-No.	⦿	↔	⦿	⦿	⦿
08921 4	6.0	166	6.0	11	5



Suitable for every use: the blades can be quickly combined, extended and interchanged.

## Wiha Info

### Did you already know?

TORX® Tamper Resistant screwdrivers can also be used for TORX® screws, but not vice versa.

# Wiha SYSTEM 6.

The compact allrounder.

## SYSTEM 6 Starter sets.



**281 T6** SYSTEM 6 reversible blades set, 6 pcs.  
Slotted/ Phillips/ hex/ ball end hex.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips. Blade length is adjustable from 42 - 114 mm.

Handle: SYSTEM 6 SoftFinish®-telescopic handle. ClickStop ball clamp guarantees a secure hold and rapid blade exchange.

Application: Versatile and space-saving, it fits in every toolbox.

Extra: Robust roll-up bag allows space-saving storage of tools.

Order-No.	Series	
27715 4	281 T6	1
① ①	284	SYSTEM 6 SoftFinish®-telescopic handle
⊕ ⊕	284	3.5 - 4.5 4.0 - 6.0 5.5 - 6.5
⊕ ⊕	284	PH1 - PH2
● ●	284	5 - 5

## SYSTEM 6 Magnetic set.



**481 T6** SYSTEM 6 reversible blades set, 6 pcs.  
Slotted/ Phillips/ hex/ ball end hex.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Handle: SYSTEM 6 Magnetic handle. With built-in magnetiser/ demagnetiser.

Application: Versatile and space-saving, it fits in every toolbox.

Extra: Robust roll-up bag allows space-saving storage of tools.

Order-No.	Series	
27717 8	481 T6	1
	481 M01	SYSTEM 6 Magnetic handle
① ①	284	3.5 - 4.5 4.0 - 6.0 5.5 - 6.5
⊕ ⊕	284	PH1 - PH2
● ●	284	5 - 5

## SYSTEM 6 professional sets.



**281 B11** SYSTEM 6 reversible blades set, 11 pcs.  
Slotted/ Phillips/ Pozidriv/ TORX®/ hex/ ball end hex.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips. Blade length is adjustable from 42 - 114 mm.

Handle: SYSTEM 6 SoftFinish®-telescopic handle. ClickStop ball clamp guarantees a secure hold and rapid blade exchange.

Application: Set in a rugged metal box for professional applications.

Order-No.	Series	
00623 5	281 B11	1
	284	SYSTEM 6 SoftFinish®-telescopic handle
① ①	284	4.0 - 6.0 5.5 - 6.5
⊕ ⊕	284	PH1 - PH2
⊕ ⊕	284	PZ1 - PZ2
⊗ ⊗	284	T10 - T15 T20 - T25 T30 - T40
● ●	284	4 - 4 5 - 5 6 - 6

## SYSTEM 6 Security and Topra set.



**281 B11 01** SYSTEM 6 reversible blades set, 11 pcs.  
Tri-Wing®/ Torq-Set®/ TORX® Tamper Resistant.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips. Blade length is adjustable from 42 - 114 mm.

Handle: SYSTEM 6 SoftFinish®-telescopic handle. ClickStop ball clamp guarantees a secure hold and rapid blade exchange.

Application: Set for safety screws in a rugged metal box.

Order-No.	Series	
27714 7	281 B11 01	1
	284	SYSTEM 6 SoftFinish®-telescopic handle
⊕ ⊕	284	TW0 - TW1 TW2 - TW3 TW4 - TW5
⊕ ⊕	284	TS2 - TS4 TS6 - TS8
⊗ ⊗	284	T6H - T8H T7H - T9H T10H - T15H T20H - T25H T30H - T40H



**281 T6 01** SYSTEM 6 reversible blades set, 6 pcs.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips. Blade length is adjustable from 42 - 114 mm.

Handle: SYSTEM 6 SoftFinish®-telescopic handle. ClickStop ball clamp guarantees a secure hold and rapid blade exchange.

Application: Versatile and space-saving, it fits in every toolbox.

Extra: Robust roll-up bag allows space-saving storage of tools.

Order-No.	Series	
32298 4	281 T6 01	1
	284	SYSTEM 6 SoftFinish®-telescopic handle
① ①	284	4.0 - 6.0
⊕ ⊕	284	PH1 - PH2
⊕ ⊕	284	PZ1 - PZ2
⊗ ⊗	284	T10 - T15 T20 - T25

## Wiha Info

### SYSTEM 6 Magnetic.

The ideal set for magnetising or demagnetising screwdriver blades and similar tools made of steel.



**282 B11-1** SYSTEM 6 reversible blades set, 11 pcs.  
Slotted/ Phillips/ Pozidriv/ TORX®/ hex/ ball end hex.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Handle: SYSTEM 6 Topra ratchet. With anti-clockwise rotation, clockwise rotation and locked position.

Application: Set with ratchet handle in a rugged metal box for professional applications.

Order-No.	Series	
03773 4	282 B11-1	1
	282	SYSTEM 6 Topra ratchet
① ①	284	4.0 - 6.0 5.5 - 6.5
⊕ ⊕	284	PH1 - PH2
⊕ ⊕	284	PZ1 - PZ2
⊗ ⊗	284	T10 - T15 T20 - T25 T30 - T40
● ●	284	4 - 4 5 - 5 6 - 6



**SB 282 122** SYSTEM 6 Topra set, 12 pcs.  
With 1/4" bit holder and 10 bits.

Handle: SYSTEM 6 Topra ratchet. For best user comfort and high torque transfer.

Extra: Blister packed.

Order-No.	Series	
05672 8	SB 282 122	1
	282	SYSTEM 6 Topra ratchet
	7802	SYSTEM 6 bit holder
①	7010 Z	4.5x25 5.5x25 6.5x25 8.0x25
⊕	7011 Z	PH1x25 PH2x25 PH3x25
⊗	7015 Z	T10x25 T15x25 T20x25

# Wiha SYSTEM 6.

The compact allrounder.

## SYSTEM 6 sets.



**281 T11** SYSTEM 6 reversible blades set, 11 pcs.  
**Slotted/ Phillips/ Pozidriv/ TORX®/ hex/ ball end hex.**  
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
 Colour-coded Wiha ChromTop® tips.  
 Blade length is adjustable from 42 - 114 mm.  
 Handle: SYSTEM 6 SoftFinish®-telescopic handle.  
 ClickStop ball clamp guarantees a secure hold and rapid blade exchange.  
 Extra: Robust roll-up bag allows space-saving storage of tools.

Order-No.	Series		
03591 4	281 T11	1	
	284	SYSTEM 6 SoftFinish®-telescopic handle	
⓪	⓪ 284	4.0 - 6.0	5.5 - 6.5
⊕	⊕ 284	PH1 - PH2	
⊕	⊕ 284	PZ1 - PZ2	
⊛	⊛ 284	T10 - T15	T20 - T25 T30 - T40
●	● 284	4 - 4	5 - 5 6 - 6

## SYSTEM 6 sets.



**U106 T8** SYSTEM 6 nut driver set, 8 pcs.  
**Nut driver.**  
 Blade: Chrome-vanadium-molybdenum steel, through-hardened, electro-plated.  
 Adjustable blade lengths.  
 Handle: SYSTEM 6 SoftFinish®-telescopic handle.  
 ClickStop ball clamp guarantees secure hold and a quick nut driver change.  
 Extra: Robust roll-up bag allows space-saving storage of tools.

Order-No.				
27712 3	U106 T8	1		
	284	SYSTEM 6 SoftFinish®-telescopic handle		
⊙		5.0	5.5	6.0 7.0
		8.0	10.0	13.0



**U106 T12** SYSTEM 6 nut driver set, 12 pcs.  
**Nut driver.**  
 Blade: Chrome-vanadium-molybdenum steel, through-hardened, electro-plated.  
 Adjustable blade lengths.  
 Handle: SYSTEM 6 SoftFinish®-telescopic handle.  
 ClickStop ball clamp guarantees secure hold and a quick nut driver change.  
 Extra: Robust roll-up bag allows space-saving storage of tools.

Order-No.				
27713 0	U106 T12	1		
	284	SYSTEM 6 SoftFinish®-telescopic handle		
⊙		4.0	4.5	5.0 5.5
		6.0	7.0	8.0 9.0
		10.0	11.0	13.0

# Wiha SYSTEM 4.

Ideal for precision work.



Colour-coded ChromTop® tips for maximum clarity.

Due to its versatility and quality the Wiha **SYSTEM 4** is a reversible blade system that convinces every user. Either for slotted, Phillips, TORX® or hex screws, the wide product range provides the right model for every application. All reversible blades are made of high-quality CVM-steel, through hardened and chrome-plated, which provides an extra long service-life.

The Wiha ChromTop® tips guarantee a perfect fit every time. Just choose from the SYSTEM 4 products for the relevant tool. Following handles are offered.


- The ergonomic **SoftFinish® telescopic handle.**
- The dissipative **SoftFinish® ESD handle.**

Each with adjustable blade lengths from 18 – 90 mm.

We offer SYSTEM 4 sets in compact roll-up pouches, rugged metal and easy access plastic boxes.



Convincing variety and quality. SYSTEM 4 – a real multi-tasker.



With the SoftFinish® telescopic handle, the blade length can be adjusted from 18 – 90 mm.

## Wiha SYSTEM 4.

- Flexible, versatile reversible precision blade system
- Sets in compact roll-up pouches, rugged metal- or easy access plastic-boxes
- Ergonomic handles for almost every application
- Colour-coded blades made of high-quality, tough chrome-vanadium-molybdenum steel, through-hardened, chrome-plated
- Wiha ChromTop® tips ensure a perfect fit every time