

## USB-C to DVI Adapter

StarTech ID: CDP2DVI



This USB-C™ to DVI adapter lets you output DVI video from a USB Type-C™ device such as a MacBook, Chromebook™ or Dell XPS™ laptop. The adapter works with USB-C devices that pass a DisplayPort video signal and it's also compatible with Thunderbolt™ 3 ports.

### Ultimate portability

This USB Type-C™ video adapter is highly portable, with a small footprint and a lightweight design. It's the perfect accessory for your MacBook or Chromebook, fitting easily into your laptop bag or carrying case, which is great for BYOD (Bring Your Own Device) applications at the office.

### Crystal-clear picture quality

The adapter supports dual-link video resolutions up to 2560x1600. You'll be surprised at the picture quality the adapter provides, even when connected to a DVI monitor, projector or television. The adapter harnesses the video capabilities that are built into your USB Type-C connection, to deliver every detail in stunning resolution.

### Hassle-free connections with USB Type-C

This adapter lets you enjoy the versatility of your portable device's USB-C port. USB Type-C is a reversible connector, so it doesn't matter which way you plug it in, the adapter will always work.

The CDP2DVI features a black housing that looks great with your ChromeBook Pixel and is backed by a StarTech.com 2-year warranty and free lifetime technical support.

#### Notes:

Your USB-C equipped device must support video to work with this adapter.

Some legacy DVI monitors may be limited to a resolution of 1920x1200 when used with this adapter.

## Applications

- Keep the adapter with you while traveling, to connect to any DVI monitor or projector you come across
- Connect your BYOD MacBook or Chromebook to a provided DVI display at work
- Walk into any boardroom with your USB-C laptop ready to present
- Connect a DVI display to your USB-C laptop to use as a secondary monitor

## Features

- Hassle-free connection with the reversible USB-C connector
- Maximum portability with a small footprint and a lightweight design
- Thunderbolt 3 port compatible
- Crystal-clear picture quality with support for video resolutions up to 2560x1600

Technical Specifications

Warranty	2 Years
Converter Type	Format Converter
Output Signal	DVI-D (DVI Digital)
Ports	1
<b>Note</b>	Some legacy DVI monitors may be limited to a resolution of 1920x1200 when used with this adapter
Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600
Connector A	1 - USB-C (24 pin) Male Input
Connector B	1 - DVI-I (29 pin) Female Output
Humidity	5~95% RH (Non-condensing)
Operating Temperature	0°C to 70°C (32°F to 158°F)
Storage Temperature	-10°C to 80°C (14°F to 176°F)
Product Weight	31 g [1.1 oz]
Shipping (Package) Weight	0 kg [0.1 lb]
Included in Package	1 - USB-C to DVI adapter

## Certifications, Reports and Compatibility

