

A793 - Needle Resistant F10 Latex Crinkle Glove

Collection: Specialist Gloves

Range: Hand Protection

Materials: HPPE, Steel, Nylon, Cotton, Elastane, Rubber

Dipping: - 100.0000%

Outer Carton: 48

Product information

The Steel Mesh reinforcement enhances the highest cut-level ANSI A9 liner by offering superior needle protection. Its unique mesh construction delivers both maximum protection and level 5 dexterity, without compromise. The palm is equipped with impressive level 5 needle resistance, while the fingers offer level 2 protection. The Latex Crinkle finish improves grip in wet and oily environments, enabling the user to work effectively on-site and handle slippery, lubricated materials.

Specialist Gloves

The Portwest Pro range is a combination of highly specialised gloves which have been designed for very specific tasks. The use of these gloves with the right task will perform better than any other glove which has been designed for more general purposes.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5
EN 388: 2016 + A1: 2018 (3X44F)
ASTM F2878:2019 Level 5
ANSI/ISEA 105: 2016 CUT Level (A9)
ANSI/ISEA 105: 2016 ABRASION Level (3)
ANSI/ISEA 105: 2016 PUNCTURE Level (5)



Features

- Tough 10 gauge liner
- Level F cut resistance
- Level 5 puncture resistance against hypodermic needles
- Crinkle latex grip offers excellent grip
- Increased puncture resistance properties
- Protects from glass, blades and abrasions
- Retail tag which aids presentation for retail sales



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A793 - Needle Resistant F10 Latex Crinkle Glove
Commodity Code: 6116108091

Test House

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A793K8RS	Black	57.0	35.0	25.0	0.9990	0.0499	5036108450480	15036108937933
A793K8RM	Black	57.0	35.0	25.0	0.9990	0.0499	5036108450473	15036108937926
A793K8RL	Black	57.0	35.0	25.0	0.9990	0.0499	5036108450466	15036108937919
A793K8RXL	Black	57.0	35.0	25.0	0.9990	0.0499	5036108450497	15036108937940
A793K8RXXL	Black	57.0	35.0	25.0	0.9990	0.0499	5036108450503	15036108937957
A793K8RXXXL	Black	57.0	35.0	25.0	0.9990	0.0499	5036108450527	15036108937964