

Tool set - SF-SL/PH SET VDE - 1212539

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Screwdriver set, bladed/crosshead Phillips Recess®, VDE insulated, 6-part, incl. rack



Why buy this product

- The SF-SL ... screwdriver sets are available with a variety of contents
- Wall-mountable screwdriver rack included

Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 589741 |
| Weight per Piece (excluding packing) | 566.8 g |
| Custom tariff number | 82054000 |
| Country of origin | Czech Republic |

Technical data

| | |
|--------------|----------|
| Product type | Tool set |
| Approval | GOST |

Articles in set

Screwdriver - SZS 0,4X2,5 VDE - 1205037



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

Tool set - SF-SL/PH SET VDE - 1212539

Articles in set

Screwdriver - SZS 0,6X3,5 VDE - 1212602



Screwdriver, slot-headed, VDE insulated, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

Screwdriver - SZS 0,8X4,0 VDE - 1212508



Screwdriver, slot-headed, VDE insulated, size: 0.8 x 4.0 x 100 mm, 2-component grip, with non-slip grip

Screwdriver - SZS 1,0X5,5 VDE - 1209114



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 5.5 x 125 mm, 2-component grip, with non-slip grip

Screwdriver - SZK PH1 VDE - 1205150



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

Screwdriver - SZK PH2 VDE - 1205163



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 21043074 |
| eCl@ss 4.1 | 21043074 |

Tool set - SF-SL/PH SET VDE - 1212539

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.0 | 21040290 |
| eCl@ss 5.1 | 21040290 |
| eCl@ss 6.0 | 21040290 |
| eCl@ss 7.0 | 21040290 |
| eCl@ss 8.0 | 21040290 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000149 |
| ETIM 5.0 | EC000149 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 27111701 |
| UNSPSC 7.0901 | 27111701 |
| UNSPSC 11 | 27111701 |
| UNSPSC 12.01 | 27111701 |
| UNSPSC 13.2 | 27111701 |

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

| |
|--|
| GOST  |
|--|