

braking resistor - 72 ohm - 400 W - cable 2 m - IP65

VW3A7607R20

- ! Discontinued on: Aug 27, 2020
- ! To be end-of-service on: Aug 15, 2025

① Discontinued

Main

| Range of product | Altivar | |
|---------------------------|--|--|
| | Lexium | |
| Range compatibility | Lexium 32 | |
| | Lexium 52 | |
| | Lexium 28 | |
| | Lexium 05 | |
| | Lexium 15 | |
| | Lexium 32i | |
| | Easy Lexium 16 | |
| Product compatibility | Motion servo drive LXM16D at 0.1 kW, 200230 V, single phase | |
| | Motion servo drive LXM16D at 0.2 kW, 200230 V, single phase | |
| | Motion servo drive LXM16D at 0.4 kW, 200230 V, single phase | |
| | Motion servo drive LXM16D at 0.75 kW, 200230 V, single phase | |
| | Motion servo drive LXM16D at 1 kW, 200230 V, single phase | |
| | Motion servo drive LXM16D at 1.5 kW, 200230 V, single phase | |
| Product or component type | Braking resistor | |
| Ohmic value | 72 Ohm | |

Complementary

| 20mpromortary | | |
|------------------|--|--|
| Energy peak | 15500 J at 480 V | |
| | 16200 J at 400 V | |
| | 24700 J at 230 V | |
| | 36600 J at 115 V | |
| Continuous power | 400 W | |
| Protection type | Thermal protection via the servo drive | |
| Net weight | 1.47 kg | |
| Cable length | 2 m | |

Environment

| IP degree of protection | IP65 |
|---------------------------------------|----------|
| Ambient air temperature for storage | -2585 °C |
| Ambient air temperature for operation | 050 °C |

Packing Units

| Unit Type of Package 1 | PCE |
|------------------------------|---------|
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4.5 cm |
| Package 1 Width | 40.0 cm |

| Package 1 Length | 13.0 cm | |
|------------------|---------|--|
| Package 1 Weight | 1.47 ka | |

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

| Packaging made with recycled cardboard | No |
|--|--|
| Packaging without single use plastic | No |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| SCIP Number | 735ea399-2868-47fa-83de-4130bb0137d4 |
| REACh Regulation | REACh Declaration |

Use Again


| ○ Repack and remanufacture | | |
|----------------------------|----|--|
| Take-back | No | |

VW3A7607R20

Dimensions Drawings

Braking Resistor

Dimensions



Dimensions in mm

| b | b1 | С | с1 | Н |
|-----|-----|----|----|-----|
| 257 | 216 | 30 | _ | 204 |

Dimensions in in.

| b | b1 | С | с1 | Н |
|-------|------|------|----|------|
| 10.11 | 8.50 | 1.18 | _ | 8.03 |