

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-- --

LOC

DIST

REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

P

LTR

DESCRIPTION

DATE

DWN

APVD

C1

OBSOLETE 174935-7

ECR-15-015932

30OCT2015

TS

KB

① -A- 面より2mmの範囲で測定。

② 相手ハウジングと所定の機能を満足して嵌合できること。

3. 内装するタブコンタクト型番：173633, 173645

4. 嵌合相手ハウジング型番：174952

① MUST BE KEPT BETWEEN -A- AND 2.

② TO BE MATED WITH THE PLUG HOUSING SMOOTHLY.

3. APPLIED TAB CONTACT PART NUMBER: 173633, 173645.

4. APPLIED PLUG HOUSING PART NUMBER: 174952, etc.

	V-2	WHITE 白	1-174936-1
OBSOLETE	HB	YELLOW 黄	174936-7
	HB	GRAY 灰	174936-6
	HB	BLUE 青	174936-5
	HB	BLACK 黒	174936-2
	HB	WHITE 白	174936-1
	FLAMMABILITY OF MATERIAL 使用材料難燃グレード	COLOR 色	PART NUMBER 型番

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 10/17'90

A.NAGAMINE

CHK 10/18'90

M.OHSHIMA

APVD 10/18'90

M.NOGUCHI

PRODUCT SPEC

108-5264

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

070 SERIES MULTI-LOCK CONNECTOR
20POSITION CAP HOUSING (W-W)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=174936

-

SCALE 2:1

SHEET 1 OF 1

REV C1

TOLERANCE UNLESS OTHERWISE SPECIFIED:
一般公差

0 < x ≤ 10 : ±0.2
10 < x ≤ 30 : ±0.25
30 < x ≤ 100 : ±0.3
ANGLE : ±3°
角度

DIMENSIONS:
mm

MATERIAL

PBT

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

-

1470-19 (3/11)